

WHG1 ESD Heat Gun, 2300W/230V, UK

Item No.: T0053101399

Heat gun, 2300W, 5°-step
precise digital temperature control

A Heat Gun that works as hard as you.

Weller's Swiss-engineered Professional Heat Gun with LCD Display delivers unparalleled performance, convenience and user-friendly operation. This heat gun delivers a fast heat-up time, an ESD-Safe housing, built-in overheat protection and an impressive 1000+ hours of lifetime use for tough production environments.
Its ergonomic design provides a comfortable grip, allowing you to handle it with ease. The integrated stand enables hands-free operation, enabling you to multitask with confidence. Additionally, the built-in energy saving function can reduce the lifetime cost of the gun. Experience the precision, versatility, and superior performance of Swiss engineering with Weller's Professional Heat Guns.

- ESD-Safe Housing (IEC/EN 61340-5-1)
- Swiss-engineered with a lifespan of over 1000+ hours
- 2300W, 5°-step precise digital temperature control – 80 °C/650 °C & 180 °F/1200 °F
- Air Volume (l/min) 200–550 (cfm) 7.1/19.4
- Work window lock & up to 5 presets functon
- Integrated Energy-Saving and Cool-Down Modes with timer, button, and motion sensor activation
- 67 dB(A) Noise emissio
- Durable high performance motor with ceramic heating element and overheating protection
- Perfect Balance & User-friendly ergonomic grip design
- 90° vertical stand hands-free operation

KEY FEATURES

- **ESD-Safe Housing –** According to IEC/EN 61340-5-1 Norm
- **1.000+ Hour Lifetime –** engineered for longevity in tough working environments
- **Ergonomic Grip and Perfect Balance –** for a less straining work experience and fewer downtimes
- **Energy Saving Modes –** keep the Heat Gun ready to work while reducing energy consumption
- **Ceramic Heating Element –** for a long-lasting high heat performance

TECHNICAL DATA

Power consumption	2,300 W
Mains supply voltage	230V/50/60Hz
Safety Class	Class 2
Operating Temperature	80–650 °C | 176–1202°F
Air Volume	200–550 l/min | 7.1–19.4 cfm
Noise level	67 dB(A)
Operating modes	OFF/I/II
Temperature Increment	+/- 5 °C/°F
Air Volume Presets	5
Customizable Presets	5
Weight	750 g | 26.46 oz
Overheat Protection	Yes
Cooldown Function	Yes
Standby Mode	Yes
Energy Saving Modes	Yes
Thermo Fuse	Yes
Cable length	4 m

SCOPE OF SUPPLY
1x Heat Gun ESD, 2300W/230W, 1x User Manual

Subject to technical alterations and amendments.

Weller is a registered trademark of Apex Brands, Inc. © 2026 | Specifications subject to change without notice.