Pushing Performance
Since 1945

D-Sub PushPull 9 pol, MA/FE, PVC,L=10m



Image is for illustration purposes only. Please refer to product description.

Part number	33 66 212 1000 194
Specification	D-Sub PushPull 9 pol, MA/FE, PVC,L=10m
HARTING eCatalogue	https://harting.com/33662121000194

Identification

Category	System cabling
Series	D-Sub
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	D-Sub Male Straight
Connector 2	D-Sub Female Straight
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Halogen-free Flame retardant

Version

Cable length	10 m
Number of cores	9
Core structure	AWG 26/7
Shielding	Shielded
Number of contacts	9
Locking type	PushPull

Technical characteristics

Rated voltage	300 V
Limiting temperature	-40 ... +80 °C unmoved -10 ... +80 °C moved

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Cable diameter	6 mm

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
PFAS	No
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	RoHS 2011/65/EU

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
eCl@ss	27060390 Ready-made data cable (unspecified)

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com