


8015-1 Vectorbord® Circbord™

- **Dimensions (H x W x Thick):** 4.00" x 4.00" x 0.062" (101.6mm x 101.6mm x 1.57mm)
- **Hole Diameter:** 0.042" (1.067mm) Plated Thru
- **Grid:** 0.100" x 0.100" (2.54mm x 2.54mm)
- **Circuit Pattern:** Pad per hole - both sides
- **Material:** FR4
- **UL Flammability Class:** 94V-0
- **16 Pin DIP Capacity:** 72
- **Wire-Wrap Terminals:** T44, T46, T49, T68
- **Solder Terminals:** T42-1, K24C, K31C
- **Wire-Wrap Socket Pins:** R32

Request Information →

- Pad-Per-Hole pattern one side only.
- 0.080″ diameter isolated solder pad around each hole one side only.
- Unrestricted component placement and extended area for high density applications.