USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Silver Aluminum

Product ID: CDPVGDVHDMDP



Thissilver USB-C multiportvideoadapteroffers a portable solution for connecting your USB Type-Claptopto a VGA, DVI, HDMI or Mini DisplayPort display. The adapter is also available in CDPVDHDMDPSGand CDPVDHDMDPRG.

Avoid the hassle of carrying different adapters for different displays with this 4-in-1USB-C adapter. With VGA, DVI, HDMI andmDPoutput, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions,providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI,mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The USB Type-C adapter has an aluminum housing designed to match your silver MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

TheCDPVGDVHDMDP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Operating System Independent

Applications

• Connect to virtually any display while traveling

• Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school

• Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

Features

• 4-IN-1 MULTIPORT USB-C VIDEO ADAPTER: USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible

• TOUGH & PORTABLE: Durable aluminum Silver enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms

• COMPATIBILITY: USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface 3, HP EliteBook/Spectre/ZBook, Chromebooks, TB3 MacBook Pro/Air [Note: The VGA output does not work with M1 based MacBook hosts]

• TESTED & VERIFIED: USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson

• EASY TO USE: Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

General		
	UPC	065030863094
	Package Quantity	1
	Warranty	3 Years
Special Notes / Requirements		
	Special Notes	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling
		The VGA output does not work with M1, M1 PRO, and M1 MAX MacBook hosts
	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Power		
	Power Delivery	No PD Pass-Through
Physical & Environmental		

Color	Silver
Cable Length	4.3 in [11 cm]
Product Length	4.1 in [10.5 cm]
Product Width	2.2 in [55 mm]
Product Height	0.6 in [15 mm]
Weight of Product	3.8 oz [108 g]
Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	40%-50%RH

Performance

HDR Support	No
Maximum Cable Distance To Display	49.9 ft [15.2 m]
General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
MTBF	654,111 hours
Audio Specifications	HDMI - 7.1 Channel Audio
	DVI - No Audio Support
	VGA - No Audio Support
	Mini DisplayPort - 5.1 Channel Audio
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz
Supported Resolutions	Max HDMI output: 3840 x 2160 @ 30Hz
	Max mDP output: 3840 x 2160 @ 60Hz
	HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200,

		1920 x 1080, 1280 x 720
		DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2
		HDMI 1.4
	Wide Screen Supported	Yes

Hardware

	Active or Passive Adapter	Active
	AV Input	USB-C
	AV Output	DVI-I (Digital Only) - Single-Link
		HDMI - 1.4
		VGA
		Mini DisplayPort - 1.2
	Number of Displays	1
	Chipset ID	Cypress - CYPD1120
		Cypress - CY7C65210
		Parade - PS8348B
		Parade - PS171

Packaging & In-the-Box

	Included in Package	1 - travel A/V adapter
	Package Width	6.9 in [17.6 cm]
	Package Depth	5.7 in [14.5 cm]
	Package Height	1.3 in [32 mm]
	Shipping (Package) Weight	6.1 oz [174 g]

Connector(s)

	Connector 1 (Quantity)	1

Connector 1	USB-C DP++ (DP Alt-Mode)
Connector 2 (Quantity)	1
Connector 2	Mini DisplayPort
Connector 3 (Quantity)	1
Connector 3	VGA
Connector 4 (Quantity)	1
Connector 4	DVI-D Dual-Link (25-Pin)
Connector 5 (Quantity)	1
Connector 5	HDMI

***Product appearance and specifications are subject to change without notice.**