

Hi-Spot - Mains Voltage Tungsten Halogen



- Very high quality 240V mains halogen lamps
- Brilliant light without the need of a transformer
- Compact size
- E27 lamp base
- 3,000 hours average rated life

Colour Temperature (K)	Max. Luminous Intensity (cd)	Power Rating (W)	Dimensions – L x Dia. (mm)	Order Code
2900	3500	100	136 x 120	471-7922
2900	3500	100	91 x 95	471-7880