HUBER+SUHNER® DATA SHEET Coaxial PCB Connector: 82_MCX-75-0-5/111_N



Description

Straight PCB jack

Interface Standards SUHNER-MCX75



 $\begin{array}{ll} \text{Impedance} & 75~\Omega \\ \text{Interface frequency max.} & 6~\text{GHz} \end{array}$

Mechanical Data

Board mounting type through holes Weight 0.0007 kg

Environmental Data

Operating Temperature -55 °C to 155 °C 2002/95/EC (RoHS) compliant

Material Data

Piece PartsMaterialCentre contactCopper Beryllium AlloyOuter contactBrass

Outer contact Brass
Body Brass
Insulator PFA / PTFE

Related Documents

Outline drawing DOU-00012964 Catalogue drawing DCA-00012966

Ordering Information

Bulk 100 pcs package 82 MCX-75-0-5/111 NH

Surface Plating

Gold Plating (Nickel underplated) Gold Plating (Nickel underplated) Gold Plating (Nickel underplated)

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions

HUBER+SUHNER
HUBER+SUHNER AG

RF Technology 9100 Herisau, Switzerland Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 www.hubersuhner.com

Document: DOC-0000193157 H Issued: 30.10.07 Uncontrolled Copy Page 1/1