

Lamps



Halogen

Total Light Output	Supply Voltage	Current Rating	Average Bulb Life	Lamp Base Type	External Height	Mftrs. Part No.
35lm	2.8V	0.85A	10h	P13.5s	32mm	1325100H
85lm	5.2V	0.85A	25h	P13.5s	32mm	1325300H
90lm	6.5V	0.7A	20h	P13.5s	32mm	1325700H
100lm	6V	1A	100h	P13.5s	32mm	1325600H

Incandescent

Total Light Output	Supply Voltage	Current Rating	Average Bulb Life	Lamp Base Type	External Height	Mftrs. Part No.
10lm	3.6V	0.3A	30h	P13.5s	32mm	1321120K
38lm	5.4V	0.54A	15h	P13.5s	32mm	1321160K