

KRAKEN SILICONE TAPE

The Ultimate Multi-Purpose Repair Tape



- Fast fusing silicone, seals and repairs an almost endless list of pipes, connectors, joints and so much more.
- **In the Home:**
 - Water pipes
 - Drains
 - Guttering
 - Sink and bath connectors
 - Joints and seals
- **In the Car and Boat**
 - Radiator hoses
 - Cables and connectors
 - Exhaust repair
 - Oil lines
 - Water hoses / pipes

Tensile Strength

Up to 700psi

Temperature Range

-65°C to +260°C

Dielectric Strength

Up to 7,000V

Colour	Dimensions		Mftrs. List No.	Order Code
	Width	Length		
Clear	24mm	3.6m	RT24CLEAR	167-6617
	48mm	3.6m	RT48CLEAR	167-6624
Black	24mm	3.6m	RT24BLACK	167-6619
	48mm	3.6m	RT48BLACK	167-6625
White	24mm	3.6m	RT24WHITE	167-6620
	48mm	3.6m	RT48WHITE	167-6626
Red	24mm	3.6m	RT24RED	167-6622
	48mm	3.6m	RT48RED	167-6627