# HP PhotoSmart 230 - Printer - colour



Colour ink-jet
102 x 165 mm
Up to 3 min/page (mono) / up to 3 min/page (colour)
Capacity: 26 sheets
Hi-Speed USB

The HP PhotoSmart 230 series color inkjet printer lets you preview your photos before you print using the color LCD display. Just select color, size and format and print borderless 4 x 6-inch photos in brilliant color - up to 4800 x 1200-optimized dpi color printing on premium photo papers. Print directly from your digital camera memory card - no PC required. And it's fun to take with you to parties and events, thanks to its small, compact size. It's so simple - easy photo almost anywhere!

Dimensions (WxDxH) 22.5 cm x 22 cm x 12.5 cm
Image Enhancement Technology HP PhotoREt III
Interface Hi-Speed USB
Language Simulation PCL 3, HP PML
Localisation English / United Kingdom
Manufacturer Warranty 1 year warranty
Max Media Size (Custom) 102 mm x 165 mm
Max Media Size (Standard) 102 x 165 mm
Max Resolution ( Colour ) 1200 dpi x 1200 dpi
Media Type Plain paper, photo paper, glossy photo paper
Print Speed Up to 3 min/page - B/W ¦ Up to 3 min/page - colour
Printer Type Photo printer - ink-jet - colour
Product Description HP PhotoSmart 230 - printer - colour - ink-jet
RAM Installed ( Max ) 8 MB
System Requirements Apple MacOS 9, Microsoft Windows XP, Apple MacOS X 10.1, Microsoft Windows 98/ME/2000
Total Media Capacity 26 sheets
Weight 1.3 kg