



**SAFETY DATA SHEET**  
ULTRAGUARD BX

Page 1  
Issued: 15/05/2008  
Revision No: 3

**1. IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING**

**Product name:** ULTRAGUARD BX  
**Company name:** ROCOL  
ROCOL House  
Swillington  
Leeds  
West Yorkshire  
LS26 8BS  
ENGLAND  
Tel: +44 (0) 113 232 2700  
Fax: +44 (0) 113 232 2740  
Emergency tel: +44 (0) 113 232 2600  
Email: [customer-service@rocol.com](mailto:customer-service@rocol.com)

**2. HAZARDS IDENTIFICATION**

**Main hazards:** Harmful if swallowed. Irritating to eyes, respiratory system and skin.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

**Hazardous ingredients:** (ETHYLENEDIOXY) DIMETHANOL >60%  
EINECS: 222-720-6 CAS: 3586-55-8  
[Xn] R22; [Xi] R38; [Xi] R41; [-] R52  
• FORMALDEHYDE <1%  
EINECS: 200-001-8 CAS: 50-00-0  
[T] R23/24/25; [C] R34; [Xn] R40; [Sens.] R43

**4. FIRST AID MEASURES (SYMPTOMS)**

**Skin contact:** There may be irritation and redness at the site of contact.  
**Eye contact:** There may be irritation and pain.  
**Ingestion:** Corrosive burns may appear around the lips.  
**Inhalation:** There may be coughing and a sore throat.

**4. FIRST AID MEASURES (ACTION)**

**Skin contact:** Wash immediately with plenty of soap and water.  
**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.  
**Ingestion:** Do not induce vomiting. Consult a doctor.  
**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

**5. FIRE-FIGHTING MEASURES**

**Extinguishing media:** Use water spray to cool containers. Suitable extinguishing media for the surrounding fire should be used.  
**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.  
**Protection of fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

**6. ACCIDENTAL RELEASE MEASURES**

**Personal precautions:** Refer to section 8 of SDS for personal protection details.  
**Environmental precautions:** Do not discharge into drains or rivers.  
**Clean-up procedures:** Transfer to a closable, labelled salvage container for disposal by an appropriate method.

[cont...]

**7. HANDLING AND STORAGE**

**Handling requirements:** Avoid direct contact with the substance.

**Storage conditions:** Store in cool, well ventilated area.

**Suitable packaging:** Must only be kept in original packaging.

**8. EXPOSURE CONTROLS / PERSONAL PROTECTION**

**Hazardous ingredients:** FORMALDEHYDE

WEL (8 hr TWA): 2 ppm WEL (15 min STEL): 2 ppm

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses with side-shields.

**Skin protection:** Protective clothing.

**9. PHYSICAL AND CHEMICAL PROPERTIES**

**State:** Liquid

**Colour:** Colourless

**Odour:** Characteristic odour

**Evaporation rate:** Negligible

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Soluble

**Viscosity:** Non-viscous

**Boiling point/range°C:** 100

**Flash point°C:** >100

**Autoflammability°C:** > 200

**Relative density:** 1.25

**pH:** 7

**10. STABILITY AND REACTIVITY**

**Stability:** Stable under normal conditions.

**Conditions to avoid:** Heat.

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

**11. TOXICOLOGICAL INFORMATION**

**Routes of exposure:** Refer to section 4 of SDS for routes of exposure and corresponding symptoms.

**12. ECOLOGICAL INFORMATION**

**Mobility:** Non-volatile. Absorbed only slowly into soil.

**Persistence and degradability:** Biodegradable.

**Bioaccumulative potential:** No data available.

**13. DISPOSAL CONSIDERATIONS**

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**14. TRANSPORT INFORMATION****ADR / RID**

**UN no:** Not Classified.

**IMDG / IMO**

**UN no:** Not Classified.

**IATA / ICAO**

**UN no:** Not Classified.

**15. REGULATORY INFORMATION**

**Hazard symbols:** Harmful.



**Risk phrases:** R22: Harmful if swallowed.  
R36/37/38: Irritating to eyes, respiratory system and skin.

**Safety phrases:** S26: In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S28: After contact with skin, wash immediately with plenty of water.

**Haz. ingredients (label):** (ETHYLENEDIOXY) DIMETHANOL

**Note:** The regulatory information given above only indicates the principal regulations specifically applicable to the product described in the safety data sheet. The user's attention is drawn to the possible existence of additional provisions which complete these regulations. Refer to all applicable national, international and local regulations or provisions.

**16. OTHER INFORMATION**

**Other information:** EC Directive 1999/45/EC relating to the classification, packaging and labelling of dangerous preparations.  
EC Directive 91/155/EEC defining the laying down and detailed arrangements for the system of specific information relating to dangerous preparations.

**Risk phrases used in s.3:** R22: Harmful if swallowed.  
R38: Irritating to skin.  
R41: Risk of serious damage to eyes.  
R52: Harmful to aquatic organisms.  
R23/24/25: Toxic by inhalation, in contact with skin and if swallowed.  
R34: Causes burns.  
R40: Limited evidence of a carcinogenic effect.  
R43: May cause sensitisation by skin contact.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.