




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	RELEASED	JWM	12/2/03	HO	1/19/04	JC	1/19/04



NOTES:

- IEC61010 Ratings: 1000V CAT III  
12 Amps  
Reinforced or double insulation
- Materials: Body-Polyamide (Nylon); Plug-Bronze and Brass, Nickel plated
- Lead Wire Jacket: Extra Flexible Silicone
- Conductor: (0.75MM<sup>2</sup>)
- Temperature: -20°C to 80°C
- Color: Red



Tenma Item No.	Length Inches [cm]	Internal Resistance (mΩ)	Color
76-022	40 [100]	20	Red
76-023			Black
76-024	60 [150]	25	Red
76-025			Black

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	12/2/03
CHECKED BY:	DATE:
Hisham Odish	1/19/04
APPROVED BY:	DATE:
John Cole	1/19/04

DRAWING TITLE:  
Sheathed, Multimeter Test Leads, 4mm Right Angle

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-605	TA-605.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	