

A3

IDEAS - PLAN REALISE A PARTIR D'UN MODELE 3D
NE PEUT ETRE MIS A JOUR QUE SUR CAO

N CLIENT

N OUTIL

N D'ETUDE

MD5 SC 20 F 0 L 3

SERIES

Solder termination

NUMBER OF CONTACT:

CONTACT TYPES:

F = female

CONTACT PLATING:

0 = selective flash gold

1 = selective 15u" gold

2 = selective 30u" gold

FIXING DEVICE :

L : Latching + Jackscrews

S : jackscrews only

THREADED HOLES:

1 : UNC # 2-56

2 : UNC #4-40

3 = M2.6

FEATURES:




- Half pitch 1.27mm(.050") series
- Centronic female connector solder type for cable
- Fully EMI/RFI shielded

MATERIALS:

- Housing:
Thermoplastic P.B.T UL94V-0 black
- Contacts:
Phosphor bronze mating end selective gold plated
- Shell: Steel nickel plated over copper

ELECTRICAL:

- Current Rating: 1 Amp
- Insulation Resistance: 500M Ω /Min
- Withstanding Voltage: AC 500V/Min
- Contact Resistance: 35m Ω MAX
- Temperature Range: -55°C ~ +105°C

Amphenol Socapex
Usine de DoleECH. ENS.
N SERIE

DOSSIER

DATE DU TIRAGE

DESIGNATION

MINI D SERIES

TOL. GEN.

VOLUME PIECE

SURFACE PIECE

PROTECTION

TRAITEMENT

MATIERE

CLIENT

MODIFICATIONS

EXEC.

DATE

Approb

IND.

N INTERNE

MD5 SC 20 F

COMMUNICATION ET UTILISATION INTERDITES SAUF AUTORISATION