


Wiha PocketStar Fold Out. Press One Button for the Correct Key.





The unique opening mechanism facilitates an easy selection of the desired key size.

The 270° stop limit when working on applications with higher safety requirements puts an end to trapped fingers.



The Wiha PocketStar fold out offers optimum handling and a wide variety of uses, which are expressed in the form of many practical details.

The ingenious opening mechanism facilitates the simple selection of the required key size from the glass-fibre-reinforced holder.

Wiha solved an important demand of fold-out users: When turning a key into working position only this one moves. The remaining keys stay where they are.

The various working positions offer universal use:

- In the 180° position, the PocketStar is used as a screwdriver.
- 270° stop limit for using the tool as practical lever for high torques.
- Any position can be set between 90° and 270° for a variety of different work applications.





Product Features:

- Innovative opening mechanism for simple selection of the desired key size
- Particularly suitable for use as screwdriver when the blade axis is set at 180° or as practical lever with blade in 270° position
- Ergonomic, glass-fibre-reinforced holder guarantees the easy transfer of even the highest torques
- Can be rotated by any angle between 270° and 90° to save time when working on applications where space is tight
- 270° stop limit for higher safety puts an end to trapped fingers
- Colour-coding system for different drives and dimensional systems delivers great clarity when using several PocketStars
- Covered hex key axes prevents catching on clothes



Wiha PocketStar Fold Out. Press One Button for the Correct Key.

PocketStar for Hex Screws. Metric Sizes.



PR P7 Ballpoint hex keys in fold out holder.

With MagicRing®, in large PocketStar, 7-pcs.

Blade: Chrome-vanadium steel, through hardened, high-quality electroplated surface.

Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.

Application: Practical fold out holder for hex screws in the workplace or on the job.

To insert and remove screws from difficult and hard to reach places. Sturdy casing with opening button to assist in the selection of the required key.

MagicRing® made from spring metal holds all standard screws tight at various angles (available from 3 mm) the ballpoint enables

tight at various angles (available from 3 mm) the ballpoint enables the user to work at angles up to 25°. 310 - 6026

Order-No.	•				-68				•	_	
23031 9	2	2.5	3	4	5	6	8	184	SEVE THE	5	H

SB 369R P7 Version with hanging hole attachment.

Extra:

Order-No.	•:							_
23033 3	2	2.5	3	4	5	6	8	5

PocketStar for Hex Screws. Metric Sizes.



351 PG7 Hex keys in fold out holder. In large PocketStar, 7-pcs.

Blade: Chrome-vanadium steel, through hardened, high-quality

electroplated surface.

Handle: Ergonomic, reinforced fibreglass housing, 120 mm long.

Application: Practical fold out holder for hex screws in the workplace or on the job.

T :----

Extra:

To insert and remove screws from difficult and hard to reach places. Sturdy casing with opening button to assist in the selection of the

required key.

Order-No. ●:
23040 1 2 2.5 3 4 5 6 8 5

SB 351 PG7 Version with hanging hole attachment. 310 - 303 o



351 PK7 Hex keys in fold out holder.

In small PocketStar, 7-pcs.

Blade: Chrome-vanadium steel, through hardened, high-quality

electroplated surface.

Handle: Ergonomic, reinforced fibreglass housing, 95 mm long.

Application: Practical fold out holder for hex screws in the workplace or

on the job.

To insert and remove screws from difficult and hard to reach places.

Extra: Sturdy casing with opening button to assist in the selection of the

required key.

23037 1

Order-No.	•!		10 T					-	
23035 7	1.5	2	2.5	3	4	5	6	5	

SB 351 PK7	Version with hanging hole attachment.	310-8193
Order No		_