

## Taper and deburring countersinker sets DIN 335 type C 90° in steel case

| Description   | Article no. | Price / set<br>€ |
|---|-------------|------------------|
| Taper and deburring countersinkers DIN 335 type C 90° HSS<br>Ø 6.3 - 10.4 - 16.5 (shank Ø 10 mm) - 20.5 - 25.0 mm                           | 102 154     |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS for<br>aluminium Ø 6.3 - 10.4 - 16.5 (shank Ø 10 mm) - 20.5 - 25.0 mm             | 102 154 A   |                  |
| Taper and deburring countersinkers HSS Co 5 for stainless steel<br>Ø 6.3 - 10.4 - 16.5 (shank Ø 10 mm) - 20.5 - 25.0 mm                     | 102 154 E   |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS-TiAlN<br>Ø 6,3 - 10,4 - 16,5 (shank Ø 10 mm) - 20,5 - 25,0 mm                     | 102 154 F   |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS-TiN<br>Ø 6.3 - 10.4 - 16.5 (shank Ø 10 mm) - 20.5 - 25.0 mm                       | 102 154 T   |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS<br>Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 (shank Ø 10 mm) - 20.5 mm                     | 102 152     |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS for<br>aluminium Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 (shank Ø 10 mm) - 20.5 mm       | 102 152 A   |                  |
| Taper and deburring countersinkers HSS Co 5 for stainless steel<br>Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 (shank Ø 10 mm) - 20.5 mm               | 102 152 E   |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS-TiAlN<br>Ø 6,3 - 8,3 - 10,4 - 12,4 - 16,5 (shank Ø 10 mm) - 20,5 mm               | 102 152 F   |                  |
| Taper and deburring countersinkers DIN 335 type C 90° HSS-TiN<br>Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 (shank Ø 10 mm) - 20.5 mm                 | 102 152 T   |                  |
| Taper and deburring countersinkers ≈ DIN 335 type C 90° tungsten<br>carbide K 20 Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 (shank Ø 10 mm) - 20.5 mm | 102 152 HM  |                  |



No. 102 154 T



No. 102 152



No. 102 155

## Taper and deburring countersinker set DIN 335 type C 90° HSS CBN ground in wooden case

| Description   | Article no. | Price / set<br>€ |
|---|-------------|------------------|
| Taper and deburring countersinkers HSS<br>Ø 4.3 - 5.0 - 6.0 - 6.3 - 7.0 - 8.0 - 8.3 - 10.0 - 10.4 - 11.5 - 12.4 -<br>15.0 - 16.5 (shank Ø 10 mm) - 19.0 - 20.5 - 23.0 - 25.0 mm | 102 155     |                  |

## Taper and deburring countersinker bit set 90° HSS in steel case

| Description   | Article no. | Price / set<br>€ |
|---|-------------|------------------|
| Taper and deburring countersinker bits HSS<br>Ø 6.3 - 8.3 - 10.4 - 12.4 - 16.5 - 20.5 mm<br>+ 1 universal handle with ¼" hexagon socket | 102 319     |                  |



No. 102 319