

Stainless Steel Compression Spring Kit - Right Hand Helix



Manufacturer: SPRINGMASTERS

Order Code: 703-3310

Manufacturer Part No: KITSC1

Wire Diameter (mm)	External Diameter (mm)	Min Working Length (mm)	Min Working Length Load	Free Length (mm)	Spring Rate	No. of Coils	Manufacturers Part Number	Order Code
0.3	2.24	6.6	4.9	15.88	0.53	20.8	C6600660	7031063
0.36	4.57	4.6	3.5	25.4	0.17	12.3	C6601040	7031075
0.4	5.4	3.6	4.1	24.9	0.2	8.5	D21070	7031087
0.41	3.05	8.2	7.8	19.05	0.72	19.1	C6601160	7031099
0.41	4.57	5.9	5.3	25.4	0.27	13.8	C6601310	7031105
0.46	4.57	5.4	7.8	19.05	0.57	11.1	C6601570	7031117
0.51	4.57	12	10.4	38.1	0.4	22.5	C6602050	7031129
0.51	6.1	4.2	6.3	15.88	0.54	7.9	C6602290	7031130
0.56	4.57	6.4	1.6	15.88	1.43	10.8	C6602740	7031166
0.56	5.33	12.3	10	38.1	0.39	20.9	C6602960	7031180
0.61	6.1	3.5	12.4	9.53	2.05	5.4	C6603910	7031191
0.61	6.1	7.2	13.9	25.4	0.76	11.2	C6604000	7031208
0.61	6.1	10.1	14	38.1	0.5	15.8	C6604020	7031210
0.61	6	8.5	12.3	27.5	0.65	13.3	C6603850	7031221
0.66	5.33	9.1	15.8	20.62	1.38	13.2	C6604310	7031233
0.74	6.1	14.1	23.8	38.1	0.99	18.1	C6605460	7031245
0.74	4.57	27.2	31.2	50.8	1.32	35	C6605340	7031257
0.74	4.57	20.7	30.9	38.1	1.77	26.6	C6605320	7031270
0.8	8.8	7.1	19.9	32	0.8	8.5	D21770	7031294
0.81	7.62	8.9	22.2	25.4	1.35	10.5	C6606730	7031300
0.81	9.14	9	21.2	38.1	0.73	10.6	C6606930	7031312
0.81	9.14	5.5	23.4	22.23	1.4	6.5	C6606870	7031324
0.81	9.14	7.4	22.9	31.75	0.94	8.7	C6606910	7031336
0.89	9.14	14	26.1	50.8	0.71	15	C6607320	7031348
0.89	9.14	6.4	24.5	19.05	1.93	6.8	C6607220	7031350
0.94	7.5	15.7	40.3	40	1.66	15.9	C6607700	7031361
1.02	7.62	17.5	44.4	38.1	2.15	16.3	C6609250	7031373
1.02	6.1	23.1	51.6	38.1	3.45	21.6	C6609060	7031385
1.02	9.14	11.7	37.3	31.75	1.86	10.9	C6609410	7031397
1.02	13.72	8.2	22.7	38.1	0.76	7.7	C6609540	7031403
1.02	9.14	13.7	37.3	38.1	1.53	12.8	C6609430	7031415
1.14	7.62	19.8	66.2	38.1	3.61	16.5	C6611220	7031427
1.17	9.91	21.7	43	50.8	1.48	17.7	C6612000	7031439
1.19	15	20.9	26	80	0.44	16.7	C6612450	7031440
1.19	10.67	18.1	52	50.8	1.59	14.5	C6612300	7031464
1.25	13.75	16.4	63	90.5	0.85	12.5	D22280	7031476
1.3	10.8	23.8	64.2	60	1.77	17.4	C6612830	7031488
1.4	12	23.7	68.7	60	1.89	16.1	C6613330	7031490
1.4	12.19	64.8	29.6	76.2	1.39	20.1	C6613500	7031506
1.6	15	16.8	79.8	45	2.83	10	C6614770	7031520