

Title: IEC D, F and G female, standardpackaging.

1. <u>DESCRIPTION</u>

Packaging the following IEC connectors:

- D-female
- F-female
- · G-female

2. MATERIAL

Tray	PN.	165939 - 2
Cover	PN.	165939 - 1
Label	PN.	999641 - 1
Sleeve (carton sleeve)	PN.	165835 - 2
Shippingbox	PN.	165882 - 0
Aircapfoil	PN.	165941 - 1
Perforationsheet	PN.	165951 - 1
Label (shippingbox)	PN.	999639 - 1

3. PACKAGINGMETHOD

FILLING THE TRAY.

- Place the tray on the machine.
- Slide the connectors into the tray.
- · Place the cover on the tray.
- Place the tray + cover with the tray upwards on a pallet with a maximum of 4 layers per pallet.

PACKAGING THE TRAY + COVER IN THE SHIPPINGBOX.

- Put a label on the front of the cover with the following information: PN. and the number of products.
- Slide 1 tray + cover into the sleeve.
- Put up the shippingbox and close the bottom with tape.
- Cover the inside of the shippingbox with a piece of approximately 40 cm of aircapfoil (the longest side parallel to the longest side of the box).
- · Place 4 filled sleeves into the shippingbox.
- Fold the ends of the aircapfoil over the sleeves and fold them between the sides of the shippingbox and the sleeves.

DR. Name	B. Colpaert	DATE 27 Sep 2002	APVD Name B. Colpaert	EC SR10-0411-02	DATE 27 Sep 2002

- Cut another piece of aircapfoil of approximately 40 cm.
- Place the foil in a 90 degree angle on top of the other piece of aircapfoil.
- Fold the aircapfoil between the sides of the box and the sleeves.
- Put 2 sheets of aircapfoil in the box.
- · Close the shippingbox with tape.
- Put a label on the box with the following information: PN., description, FO-number, production-date and the number of products in the shippingbox.

4. STANDARDPACKAGINGQUANTITY

Туре	Tray (= PPQ)	Doos (= APQ)
D-female	27	108
F-female	20	80
G-female	15	60

PACK. TY = TYA

5. PSEUDO PN.

PSEUDO PN.: 0-0215995-4

			(U=3)
DNI	405000	_	4000 0000
PN.	165939 -	2	4000.0000
PN.	165939 -	1	4000.0000
PN.	999641 -	1	4000.0000
PN.	165835 -	2	4000.0000
PN.	165882 -	0	1000.0000
PN.	165941 -	1	800.0000
PN.	165951 -	1	2000.0000
PN.	999639 -	1	1000.0000