

Kroy Product List

PART NO.	DESCRIPTION
2227516	General Purpose Cartridge - Black on White for 244RS
2357516	Industrial Cartridge - Black on White for 244RS
2357543	Industrial Labeling Cartridge - Black on Yellow Fits Kroy 240 Series
2383211	Duratype 244RS Label Machine with 120V Adapter
2438616	Industrial UV Cartridge, 1 Inch - Laminated Black on White For K2500
2438620	1" White/Black Fits K2500/3000
2438626	1.0 Inch UV Laminate Labeling Cartridge - Black on Gold Fits K200, K2500, K3000-PC
2438632	1.0 Inch UV Laminate Labeling Cartridge - White on Blue
2438636	1.0 Inch UV Laminate Labeling Cartridge - White on Red Fits K2000, K2500, K3000-PC
2438640	White on Green, 1" X 40" For K2500/K3000
2438643	Black on Yellow, 1" X 40" For K2500/K3000
2438716	Industrial UV Cartidge, 0.8 Inch - Laminated Black on white for K2500
2504210	K2500 Label Machine - 120V NICAD Batteries - Battery Charger
2526704	.75 Inch Labeling Cartridge - Black On White Fits K750
2526705	Tape 3/4" Red/White
2526706	Tape 3/4" Black/Red
2526709	Tape 3/4" Black/Yellow
2526714	.75 Inch Labeling Cartridge - White on Red Fits K750
2526804	1.0 Inch Labeling Cartridge - Black on White Fits K750
2554400	K3000-PC



2526714



2438701



2438701



2526709



2526804

**DuraType 244RS/240SE**

**DuraType 244RS** - Four-line printing capability - Set label length function - Left, right and center justified text - Word out function - Feed control which allows the adjustment of tape feed between labels - Built-in typeface corresponding to the Helvetica Regular typestyle in 8 and 12 point type size and 3 of 9 bar code.

**DuraType 240SE** - Portable labeling system with thermal-transfer printing capabilities - 240 DPI resolution - Resident 8, 12, 24 point Helvetica Regular, 36 point Helvetica bold, and 12 point Times Roman - Double-line printing - Outline - Bold - Frame - Vertical expand/condense - Mirror function and shadow - Negative image - Word-out function - Feed control which allows the adjustment of tape feed between labels.

**DuraType 244RS/240SE includes:** (1) Printer, (1) AC Adapter and Owner's Manual. *Printers do not come with supply cartridge.* Printers operate on batteries or AC adapter.

**General Purpose Label Supply**

<b>Labeling</b>	<b>.50"x.50'</b>	<b>Labeling</b>	<b>.50"x.50'</b>
Black image on clear	2227501	Black image on blue	2227531
White image on clear	2227502	White image on blue	2227532
Blue image on clear	2227503	Black image on red	2227535
Red image on clear	2227504	White image on red	2227536
Black image on white	2227516	Black image on green	2227539
Blue image on white	2227517	White image on green	2227540
Red image on white	2227518	Black image on yellow	2227543
Green image on white	2227519	Black image on orange	2227548
White image on black	2227520	White image on orange	2227549
Black image on silver	2227521	Architectural and Engineering	2227553
Black image on gold	2227526		

**Industrial Label Supply**

<b>Labeling</b>	<b>.50"x.50'</b>	<b>Labeling</b>	<b>.50"x.50'</b>
Black image on clear	2357501	White image on blue	2357532
White image on clear	2357502	Black image on red	2357535
Black image on white	2357516	White image on red	2357536
White image on black	2357520	Black image on green	2357539
Black image on silver	2357521	White image on green	2357540
Black image on gold	2357526	Black image on yellow	2357543
		Black image on orange	2357548

**Badge Label Supply**

**For Laminated Badges .50"x.50'**

Black image on clear	2360401
Black image on white	2360402

**Special Purpose Label Supply**

	<b>.50"x.50'</b>
White image on black (matte finish)	2472801

**Typestyle Cards**

<b>Fonts Similar To:</b>	6 pt.	8 pt.	10 pt.	12 pt.	14 pt.	16 pt.	18 pt.	24 pt.	30 pt.	36 pt.
Calligraphy						2418807	2418808	2418809		
Helvetica Regular	2226401	2226402	2226403	2226404	2226405	2226406	2226407	2226409	2226472	2226410
Helvetica Medium	2226421	2226422	2226423	2226424	2226425	2226426	2226427	2226429	2226471	2226430
Helvetica Bold							2226437	2226439	2226474	2226440
Condensed Vertical Helvetica Medium						2226456		2226459	2226460	
Times Roman	2226511	2226512	2226513	2226514	2226515	2226516	2226517	2226519	2226541	2226520
Time Roman	2226542 (10/12 pt.)		2226543 (6/8/12 pt.)							

**Bar Code Symbology Cards**

3 of 9 Bar Code	2315800	EAN 8/13	2315806
I2 of 5	2315803	CODABAR	2315807
UPC-A	2315804	3 of 9 High Density	2315815

**Specialty Fonts**

US Postal	2315805
-----------	---------

**Accessories**

AC Adapter (115 V)	2476800
Battery Charger	2452500
Thermal Printhead Cleaning Kit (25)	2559000
Carrying Case**	2387700

\*\*Machine Carrying Case is capable of holding the following: 240 series printer, AC Adapter or Battery Charger, up to 5 Tape Cartridge and 6 Font Cards.

## Kroy

### K750

**K750** - 5 label widths from 1/4" to 1" - Eight-line capacity - Create customized address, video, diskette, and warning labels with built-in templates - 4 fonts including (Helvetica, Gothic, Script, Roman) - 7 type sizes from 6 to 48 point and 11 different type styles - 8 resident bar codes - Auto-character height - Auto label-size sensing - Print preview - Over 200 clip-art images.

**K750 includes:** (1) Printer, (6) AA Batteries, (2) Supply Cartridge and Owner's Manual.

<b>1/4" Label Supply</b>	<b>1/4"x26'(6.35mmx7.6m)</b>	<b>3/4" Label Supply</b>	<b>3/4"x26'(19.05mm x 7.6m)</b>
Black image on clear	2526401	Black image on clear tape	2526701
Black image on white	2526404	Black image on white tape	2526704
Black image on red	2526406	Red image on white tape	2526705
		Black image on red tape	2526706
<b>3/8" Label Supply</b>	<b>3/8"x26' (9.53mm x 7.6m)</b>	Black image on yellow tape	2526709
Black image on clear	2526501	White image on red tape	2526714
Black image on white	2526504	White image on black tape	2526719
Black image on yellow	2526509		
Black image on blue	2526511	<b>1" Label Supply</b>	<b>1" x 26' (25.4mm x 7.5m)</b>
<b>1/2" Label Supply</b>	<b>1/2" x 26' (12.7mm x 7.6m)</b>	Black image on clear	2526801
Black image on clear	2526601	Black image on white	2526804
Black image on white	2526604	Black image on yellow	2526809
Black image on red	2526606	Black image on blue	2526811
Black image on yellow	2526609	White image on red	2526814
White image on red	2526614		

#### Accessories

AC Adapter (115V) 2476800

### K2500/K3000-PC

**K2500** - Portable thermal printer - 203 DPI resolution - Resident type style corresponding to Helvetica - Resident bar code symbologies: 3 of 9, 12 of 5, 128, UPC-A, UPC-E, EAN-8, EAN-13, CODABAR, code 39, code 128, check digit calculation - One to six line printing - 67 type sizes from 6 point to 72 point in single point increments (1/16" to .75") - Underline - Bold - Frame - Italic - Mirror - Vertical - Label formatting - Auto-repeat (1-999) - Alpha and numeric sequencing - 6000 character memory - Auto shut-off - RS 232 port - Left, right and center justified text function - Line identification function - Line out function - Feed control - Audible key clicks and error messages - Real-time clock - PDF-417 - MSI-Plessey - Prints on a wide variety of media.

**K2500 includes:** (1) Printer with the protective jacket, (6) Ni-Cad C-Cell Batteries, (1) Battery Charger and Owner's Manual. *Printers do not come with supply cartridge.* K2500 operates on batteries or AC adapter.

#### K2500 Accessories

(6) Standard NiCd Batteries 2449300  
 AC Adapter (120V) 2435100  
 Carrying Case 2447100  
 Battery Charger 2452500  
 Thermal Printhead Cleaning Kit (25) 2559000

**K2500 Extended Warranty EWPK2500**

#### K3000-PC Desktop Label Printer

**K3000-PC** - Compact thermal transfer printer - 300 DPI resolution - Connects to personal computer running Windows 95, 98, 2000 or NT 4.0 - comes with Kroy Label Designer Software to print logos, bar codes and data - 25 resident bar codes - Sequential printing capabilities - Prints labels up to 14" in length - Supplies compatible with K2500.

**K3000-PC includes:** (1) Printer, (1) AC Adapter, (1) Serial Cable, KLDS Software and Print Driver Diskette. *Printers do not come with supply cartridge.*

#### K3000-PC Accessories

Serial Cable 2558800  
 AC Adapter (120V) 2556600  
 Thermal Printhead Cleaning Kit (25) 2559000

**K3000PC Extended Warranty EWPK3000PC**

**K2500/K3000-PC Con't**

**Polyester Industrial Label Supply**

2.0 mil pressure sensitive polyester and thermal transfer resin ribbon in a cartridge - Up to 7 year exterior life; chemical, water, UV and abrasion resistant. Operating temperature range of -40 degrees to 320 degrees Fahrenheit (160 degrees Celcius) - High performance label stock.

**Industrial UV & Chemical Resistant Cartridge Supply  
.375" x 40'**

Black image on clear	2560101
Black image on white	2560116
Black image on yellow	2560143

**Industrial UV & Chemical Resistant Cartridge Supply  
.50" x 40'**

	Old Part No.	New Part No.
Black image on clear	2558501	2487901
Black image on white	2558516	2487916
Black image on yellow	2558543	2487943
White image on black	NA	2487920

**Industrial UV & Chemical Resistant Cartridge Supply  
.8" x 40'**

	Old Part No.	New Part No.
Black image on clear	2438201	2438701
Black image on white	2438216	2438716
Black image on yellow	2438243	2438743

**Die-Cut Polyester Label Supply**

**Black on White - W x L**

066" x 3.44"	2438501	.375" x 1.8125"	2438508
1.0" x 4.0"	2438503	1.0" x 1.0"	2438510
.50" x 1.0"	2438504	1.0" x 2.0"	2438511
.50" x 1.50"	2438506		

**Tamper-Evident Polyester Label Supply**

3.0 mil polyester pressure sensitive that leaves a white residue with a word "VOID" if the label is removed.

1" x 40' Black on white	2483801
.50" x 40' Black on white	2487970

**Cast Vinyl Industrial Label Supply**

2.0 mil pressure sensitive vinyl and thermal transfer resin ribbon in a cartridge - Up to 10 year exterior life; chemical, water, UV and abrasion resistant - Operating temperature range of -50 degrees to 180 degrees Fahrenheit (82 degrees Celcius) - Excellent conformability to curved or irregular surfaces.

	.50" x 40'	1" x 40'
Black image on clear	2558301	2558101
Black image on white	2558316	2558116
Black image on silver	NA	2558121
Black image on blue	2558331	2558131
Black image on red	2558335	2558135
Black image on yellow	2558343	2558143



K2500