# Sunnex HM 35W

Machine and industrial lighting





## **X Sunnex**

## **Machine and** industrial lighting

Sunnex HM Flex 35W Sunnex HM Spot 35W


### **Flexible light which** dissipates heat


Sunnex HM is a small and effective workplace light which produces good, concentrated light. With a small external dimensions and flexible setting options, Sunnex HM blends in well in the working environment.

Sunnes HM has an integral electronic transformer, but is also available in a low-voltage version for direct connection to machinery. The flexible arm is of extremely high quality, and is available in 500 and 700 mm long versions. The lamp head is made of impact-resistant thermosetting plastic and supplied with ventilation holes which efficiently dissipate the heat from the halogen bulb.

### Areas of application

Examples of applications include spot lighting for manufacturing machinery and machine tools, as well as for precision mechanical work.





#### **HM 35W - SPOT**

· Single or double-jointed head

- 230V/12V with integrated transformer
- 12 or 24V direct connection

	Arm options	Connection	Other	Art. Nr.
HM 35W — FLEX	500 mm	230V	Without joint	23001
			With joint	23004
		12V	Without joint	23002
			Without joint, Dimmer	23002DIM
			With joint	23005
			With joint, Dimmer	23005DIM
		24V	Without joint	23003
			Without joint, Dimmer	23003DIM
			With joint	23006
			With joint, Dimmer	23006DIM
<b>H</b> M 35W – SPOT	Single joint	230V		23031
		12V		23024
		24V		23019
	Double joint	230V		23029
		12V		23025
		24V		23026

The above Sunnex HM light models are only a limited selection. For further model descriptions, mounting devices and accessories, see the brochure Sunnex Workplace Lightning - Technical Documentation, or contact your dealer

Manufacturer



**Nolato Sunnex Equipment AB** Box 555, SE-686 28 Sunne, Sweden Tel: +46 565-177 00 Fax: +46 565-104 00 E-mail: equipment@nolato.se Internet: www.sunnex.com Nolato Sunnex Equipment AB is certified in accordance with ISO 9001 and ISO 14001



ntally certified.

ISO 14001 environm

Grafiska -

. Alfa Nermans

annourse

NSE

HM.

000 UK

ex HM is sold in Nolato Sunnex Equip ents AB's standard ve ion. All Sun ex liahtina ins nts and in the colour black as st W is so on hovens summer suppresents As stantare version. All sunnex iggring instruments are supprised with screw mounts and in the occur oback as it If a different type of mounting device is required, look in the brochure Sunnex Workplace Lighting. – Technical Documentation, or contact your dealer, risk of injury, all assembly work should be performed by autohoside personnal with the necessary knowledge of the product, its installation and its user en We reserve the right to alter components and to make design changes. This publication replaces previous editions. To avoid the risk of injury, all as