



DB9 F I/O	SWITCH	DB9 F A&B&C&D
1	1	1
2	2	2
3	3	3
4	4	4
5	5	5
6	6	6
7	7	7
8	8	8
9	9	9
SHIELD	SHIELD	SHIELD

6	PLASTO-VISCO-ELASTIC BODY	4	M415
5	SCREW 3*6PWB	4	M805
4	METAL CASE 152*92*58mm, THICKNESS 0.8mm	1set	M415
3	UL1061 26AWG OD1.35, LENGTH 150mm	49pcs	M415
	MAIN HEART 3-9-4	1	M94
	SCREW 4*12.5mm WITH PAD	1set	M415
2	KNOB FOR A, B, C, D, SWITCH	1	TWN
	HEX-NUT 4.75*13mm, SCREW CAP 4.75*1.5	10set	M95
1	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	5	M108
No.	DESCRIPTION	Q'ty	Supplier

ITEM NO.
CST-DB9/4