



53.4	51.3	48.75	52045	40
52.15	50.05	47.5	↑	39
50.9	48.8	46.25		38
49.65	47.55	45		37
48.4	46.3	43.75		36
47.15	45.05	42.5		35
45.9	43.8	41.25		34
44.65	42.55	40		33
43.4	41.3	38.75		32
42.15	40.05	37.5		31
40.9	38.8	36.25		30
39.65	37.55	35		29
38.4	36.3	33.75		28
37.15	35.05	32.5		27
35.9	33.8	31.25		26
34.65	32.55	30		25
33.4	31.3	28.75		24
32.15	30.05	27.5		23
30.9	28.8	26.25		22
29.65	27.55	25		21
28.4	26.3	23.75		20
27.15	25.05	22.5		19
25.9	23.8	21.25		18
24.65	22.55	20		17
23.4	21.3	18.75		16
22.15	20.05	17.5		15
20.9	18.8	16.25		14
19.65	17.55	15		13
18.4	16.3	13.75		12
17.15	15.05	12.5		11
15.9	13.8	11.25		10
14.65	12.55	10		9
13.4	11.3	8.75		8
12.15	10.05	7.5		7
10.9	8.8	6.25		6
9.65	7.55	5		5
8.4	6.3	3.75	↓	4
7.15	5.05	2.5	52045	3
	B	A	ENG. NO.	