

Condensador para Iluminación Lighting Capacitor



Terminal:	Cable 200 mm	Terminal:	200 mm Leads
Fijación:	Tornillo M8	Fixing:	M8 Bottom Screw
Carcasa:	Plástico	Can:	Plastic

SERIE RI008HP_{xxx}P25

Código Code	Capacidad Capacitance µF	Tensión Voltage Vac	Diámetro Diameter mm	Longitud Length h (mm)	Und. Caja Unit Box	P.V.P. €/Und
RI008HP020P25 *	2	250	25	52	165	1,33
RI008HP030P25 *	3	250	25	52	165	1,37
RI008HP035P25 *	3,5	250	25	52	165	1,41
RI008HP040P25 *	4	250	25	52	165	1,45
RI008HP045P25 *	4,5	250	25	52	165	1,55
RI008HP050P25 *	5	250	25	70	165	1,59
RI008HP055P25 *	5,5	250	25	70	165	1,61
RI008HP060P25 *	6	250	25	70	165	1,64
RI008HP070P25 *	7	250	25	70	165	1,78
RI008HP080P25 *	8	250	30	74	110	1,91
RI008HP090P25 *	9	250	30	74	110	2,00
RI008HP100P25 *	10	250	30	74	110	2,13
RI008HP110P25 *	11	250	30	74	110	2,63
RI008HP120P25 *	12	250	30	74	110	2,74
RI008HP140P25 *	14	250	35	74	85	3,00
RI008HP160P25 *	16	250	35	74	85	3,25
RI008HP180P25 *	18	250	35	74	85	3,48
RI008HP200P25 *	20	250	35	98	85	3,60
RI008HP200P25B*	20	250	40	70	65	3,69
RI008HP250P25 *	25	250	35	98	85	4,44
RI008HP280P25 *	28	250	40	94	65	4,77
RI008HP300P25 *	30	250	40	94	65	5,03
RI008HP320P25 *	32	250	40	94	65	5,36
RI008HP350P25 *	35	250	40	94	65	5,74
RI008HP400P25 *	40	250	50	98	40	6,26
RI008HP450P25	45	250	50	98	40	7,11
RI008HP500P25	50	250	50	98	40	7,67
RI008HP550P25	55	250	50	98	40	8,28
RI008HP600P25	60	250	50	98	40	8,86

Se suministran otras capacidades bajo demanda / Other capacitance under demand

* Homologación
* Approval



UNE-EN-61048 / AI
61049

