

19.48.071

PC Quick-Fit Terminals

Material	Bronze
Surface	Tin Plated
Hole Dia.	4,0
Broad B1	6,3 mm
Vogt AG No.	382508.28
Type designation	PC Quick-Fit Terminals
Version	4,8x0,8
Design	Straight
Contact Length	6,4 mm
PCB Hole Dia.	1,30 mm
Grid Pitch	5,00 mm
	RoHS konform

