



EN 60320-1 STANDARD SHEET C19

250V / 21A

BODY MOLDINGS - PA 6 (UL94-V0)
 CONTACTS - BRASS, NICKEL PLATED
 CONTACT SCREWS - STEEL, NICKEL PLATED
 CABLE CLAMP - STEEL, NICKEL PLATED AND PA 6 (UL94-V0)
 CABLE CLAMP SCREWS - STEEL, NICKEL PLATED
 COVER SCREW - STEEL, NICKEL PLATED
 INSERT - STEEL, NICKEL PLATED
 CABLE GUARD - PVC (UL94-V0)

REVERSIBLE CABLE
ALLOWS FOR THE

ISS.	MOD. & DATE	4	14.6.00	TOLERANCES X.X +/- 0.4	MATL	SCALE
1	18.1.00	5	17.8.00	X.XX +/- 0.1	SEE ABOVE	DO NOT
2	15.3.00			UNLESS STATED OTHERWISE	FINISH	USED ON
3	23.03.00			DIMS IN MM	SCHURTER LTD. BOGNOR REGS. UNITED KINGDOM	SHT. 1