


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO





- NOTES:**
1. RECOMMENDED CABLE DIAMETER: 0.138 ϕ THRU 0.276 ϕ
 2. IP (INGRESS PROTECTION) RATING: 67

MATERIALS:
 GASKETS: EPDM
 BODY: NYLON
 HOUSING: ABS
 O-RING: SILICONE
 SEAL: EPDM
 SEALING NUT: NYLON
 THUMBSCREW: BRASS

FINISH:
 THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY C.MCCORMICK	01/28/2004	
DIMENSIONAL TOLERANCES: .X = \pm .1 .XX = \pm .01 .XXX = \pm .005	CHECKED BY D.PARHAM	01/28/2004	CATEGORY DATA CABLING
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION HD15 FEMALE WATERPROOF CONNECTOR
ANGULAR TOLERANCES: ALL = \pm 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A
PROJECTION 	COLOR VARIATIONS MAY OCCUR	FSCM NO. 43321	DWG. NO. WPHDB15S-KIT
		SCALE: NONE	CAD FILE: WPHDB15S-KIT.SLDDRW
		SHEET 1 OF 1	

