



MODULAR

TECHNICAL HOTLINE +44 (0)1268 563720

MODULAR

SELECTION CHART

	1	2	3	4	6	8	9	12	18	24	Architrave	
<b>COVER PLATES</b>												
LOGIC PLUS	K3631 WHI 10	K3632 WHI 10	K3633 WHI 10	K3634 WHI 10	K3636 WHI 1		K3638 WHI 1		K3639 WHI 1			
METALCLAD PLUS	K3491 ALM 10	K3492 ALM 10	K3493 ALM 5	K3494 ALM 5	K3496 ALM 1		K3498 ALM 1	K3499 ALM 1	K3502 ALM 1	K3508 ALM 1	K3514 ALM 1	
ALBANY PLUS												
MCO matt chrome	K3431 MCO 10	K3432 MCO 10	K3433 MCO 5	K3434 MCO 5	K3436 MCO 1		K3438 MCO 1	K3439 MCO 1	K3442 MCO 1	K3448 MCO 1	K3454 MCO 1	K3401 MCO 10
SAB satin brass	K3431 SAB 10	K3432 SAB 10	K3433 SAB 5	K3434 SAB 5	K3436 SAB 1		K3438 SAB 1	K3439 SAB 1	K3442 SAB 1	K3448 SAB 1	K3454 SAB 1	K3401 SAB 10
CHROMA PLUS	K3431 PCR 1	K3432 PCR 1	K3433 PCR 1	K3434 PCR 1	K3436 PCR 1		K3438 PCR 1	K3439 PCR 1	K3442 PCR 1	K3448 PCR 1	K3454 PCR 1	K3401 PCR 1
GROSVENOR PLUS	K4331 POB 1	K4332 POB 1	K4333 POB 1	K4334 POB 1	K4346 POB 1		K4348 POB 1		K4352 POB 1			
SAVOY PLUS	K5331 PBS 1	K5332 PBS 1	K5333 PBS 1	K5334 PBS 1	K5346 PBS 1		K5348 PBS 1		K5352 PBS 1			
EDGE INSIGNIA (non UK)	K14331 (See Colour Key) 1	K14332 (See Colour Key) 1	K14333 (See Colour Key) 1	K14334 (See Colour Key) 1	K14346 (See Colour Key) 1		K14348 (See Colour Key) 1	K14349 (See Colour Key) 1	K14352 (See Colour Key) 1	K14358 (See Colour Key) 1	K14354 (See Colour Key) 1	K14401 (See Colour Key) 1
<b>BOXES</b>												
LOGIC PLUS flush	891 ALM 2 x 20mm knockouts 10	891 ALM 2 x 20mm knockouts 10	892 ALM 4 x 20, 4 x 25mm knockouts 5	892 ALM 4 x 20, 4 x 25mm knockouts 5	893 ALM 4 x 20, 4 x 25mm knockouts 5		893 ALM 4 x 20, 4 x 25mm knockouts 5		895 ALM 5 x 20, 5 x 25mm knockouts 1			
	821 ALM without knockouts 10	821 ALM without knockouts 10	822 ALM without knockouts 5	822 ALM without knockouts 5	823 ALM without knockouts 5		823 ALM without knockouts 5		825 ALM without knockouts 1			
LOGIC PLUS surface metal	K2213 ALM 5 x 20mm knockouts 10	K2213 ALM 5 x 20mm knockouts 10	K2214 ALM 7 x 20mm knockouts 5	K2214 ALM 7 x 20mm knockouts 5								
	K2211 ALM without knockouts 10	K2211 ALM without knockouts 10	K2212 ALM without knockouts 5	K2212 ALM without knockouts 5								
LOGIC PLUS surface moulded	K2140 WHI with knockouts 10	K2140 WHI with knockouts 10	K2142 WHI with knockouts 5	K2142 WHI with knockouts 5								
LOGIC PLUS surface pvc	K2181 WHI with knockouts 10	K2181 WHI with knockouts 10	K2183 WHI with knockouts 5	K2183 WHI with knockouts 5								
METALCLAD PLUS & ALBANY PLUS surface	K8891 ALM 5 x 20mm knockouts 10	K8891 ALM 5 x 20mm knockouts 10	K8892 ALM 7 x 20mm knockouts 5	K8892 ALM 7 x 20mm knockouts 5	K8893 ALM 4 x 20mm, 4 x 25mm knockouts 5		K8893 ALM 4 x 20mm, 4 x 25mm knockouts 5	K8895 ALM 5 x 20mm, 5 x 25mm knockouts 1	K8895 ALM 5 x 20mm, 5 x 25mm knockouts 1	K8898 ALM 5 x 20mm, 5 x 25mm knockouts 1	K8900 ALM 6 x 20mm, 6 x 25mm knockouts 1	
	K8821 ALM without knockouts 10	K8821 ALM without knockouts 10	K8822 ALM without knockouts 5	K8822 ALM without knockouts 5	K8823 ALM without knockouts 5		K8823 ALM without knockouts 5	K8825 ALM without knockouts 1	K8825 ALM without knockouts 1	K8826 ALM without knockouts 1	K8827 ALM without knockouts 1	
	K8901 ALM deep box 5 x 20mm knockouts 10	K8901 ALM deep box 5 x 20mm knockouts 10	K8902 ALM deep box 4 x 20mm, 4 x 25mm knockouts 10	K8902 ALM deep box 4 x 20mm, 4 x 25mm knockouts 10								
ALBANY PLUS CHROMA PLUS & EDGE flush	891 ALM 2 x 20mm knockouts 10	891 ALM 2 x 20mm knockouts 10	892 ALM 4 x 20, 4 x 25mm knockouts 5	892 ALM 4 x 20, 4 x 25mm knockouts 5	893 ALM 4 x 20, 4 x 25mm knockouts 5		893 ALM 4 x 20, 4 x 25mm knockouts 5	895 ALM 5 x 20, 5 x 25mm knockouts 1	895 ALM 5 x 20, 5 x 25mm knockouts 1	898 ALM 6 x 32mm knockouts 1	900 ALM 6 x 32mm knockouts 1	3895 ZIC 3 x 20mm knockouts (for flush mounting only) 5
	821 ALM without knockouts 10	821 ALM without knockouts 10	822 ALM without knockouts 5	822 ALM without knockouts 5	823 ALM without knockouts 5		823 ALM without knockouts 5	825 ALM without knockouts 1	825 ALM without knockouts 1			3891 ZIC 1 gang 2 gang Architrave Boxes for EDGE 5
GROSVENOR PLUS & SAVOY PLUS flush	891 ALM 2 x 20mm knockouts 10	891 ALM 2 x 20mm knockouts 10	892 ALM 4 x 20, 4 x 25mm knockouts 5	892 ALM 4 x 20, 4 x 25mm knockouts 5	893 ALM 4 x 20, 4 x 25mm knockouts 5		893 ALM 4 x 20, 4 x 25mm knockouts 5	895 ALM 5 x 20, 5 x 25mm knockouts 1	895 ALM 5 x 20, 5 x 25mm knockouts 1	898 ALM 6 x 32mm knockouts 1	900 ALM 6 x 32mm knockouts 1	
	821 ALM without knockouts 10	821 ALM without knockouts 10	822 ALM without knockouts 5	822 ALM without knockouts 5	823 ALM without knockouts 5		823 ALM without knockouts 5	825 ALM without knockouts 1	825 ALM without knockouts 1			
<b>GRIDS</b>												
Edge/Insignia cover plates include an integral grid	K3701 10	K3702 10	K3703 10	K3704 10	K3703 X 2 10		K3704 X 2 10	K3703 X 3 10	K3704 X 3 10	K3706 X 3 10	K3706 X 4 10	K3708 10

**COLOUR KEY**  
 All Edge frontplates (Insignia range in non UK markets) are supplied with grid module mounting frame. Add the appropriate colour suffix to the list no. eg K14331 BSS.

- BSS Brushed Stainless Steel
- PBR Polished Brass
- SAA Silver Anodised Aluminium
- POC Polished Chrome
- WHI White
- BLA Black Anodised Aluminium
- PBZ Polished Bronze
- ABR Antique Bronze
- BBR Brushed Brass
- GLD Gold Plate

See pages 182-209 for more information.