

FESTO

Data sheet

Part no. 1331 49

Page 1

QSY-6

Push-in Y connector

Feature	Description
Design structure	Push/pull principle
Ambient temperature	0 - 60 °C
Pneumatic connection	for tubing, 6mm outside diameter
Operating pressure	0,000 - 10,000 bar
Medium temperature	0,0 - 60,0 °C
Operating medium	Compressed air, filtered, unlubricated Filtered, lubricated air
Nominal size	4,800 mm
Size	Standard
Corrosion resistance classification CRC	1