

11 - Alligator Clips

Standard Alligator Clips

Material: Nickel Plated Iron, 800°C



HOFFMAN PART NO.	AMPS	LENGTH	JAW SPREAD	JAW LENGTH	INSULATION
T115	10	1.97	0.509	0.157	None
T115SR	10	1.97	0.509	0.157	Red
T115SB	10	1.97	0.509	0.157	Black
T154	5	1.22	0.193	0.138	None
T160	10	1.97	0.509	0.157	None
T160R	10	1.97	0.509	0.157	Red
T160B	10	1.97	0.509	0.157	Black

For clip with a screw add **S** to part number, i.e. **T160S**

For copper plating add **C** to part number, i.e. **T160C**

Insulators for Standard Alligator Clips


Material: PVC

HOFFMAN PART NO.	HOFFMAN CLIP PART NO.	COLOR
T154INSB	T154	Black
T154INSBL	T154	Blue
T154INSGR	T154	Green
T154INSR	T154	Red
T154INSY	T154	Yellow
T160INSB	T160	Black
T160INSR	T160	Red
T160INSW	T160	White



Charging Clips

Material: Nickle Plated Iron, 800°C



HOFFMAN PART NO.	AMPS	LENGTH	JAW SPREAD	JAW LENGTH	INSULATION	WITH SCREW
T510	10	2.0	0.43	0.39	None	N
T510SB	10	2.0	0.43	0.39	Black	Y
T510SR	10	2.0	0.43	0.39	Red	Y
T520S	20	2.5	0.67	0.51	None	Y
T520SR	20	2.5	0.67	0.51	Red	Y
T520SB	20	2.5	0.67	0.51	Black	Y
T530S	20	2.5	0.67	0.51	None	Y
T530SB	20	2.5	0.67	0.51	Black	Y
T530SBL	20	2.5	0.67	0.51	Blue	Y
T530SG	20	2.5	0.67	0.51	Green	Y
T530SR	20	2.5	0.67	0.51	Red	Y
T530SW	20	2.5	0.67	0.51	White	Y
T530SY	20	2.5	0.67	0.51	Yellow	Y
T550	50	4.1	1.50	0.51	None	Y
T550SB	50	4.1	1.50	0.51	Black	Y
T550SR	50	4.1	1.50	0.51	Red	Y
T615	15	15	0.48	0.39	None	N
T615B	15	15	0.48	0.39	Black	N
T615R	15	15	0.48	0.39	Red	N
T6410C*	100	5.91	0.676	0.866	None	N
T6410CB*	100	5.91	0.676	0.866	Black	N
T6410CR*	100	5.91	0.676	0.866	Red	N
T641CP	30	2.95	1.06	0.433	None	N
T641CPB	30	2.95	1.06	0.433	Black	N
T641CPR	30	2.95	1.06	0.433	Red	N
T641CPC*	75	2.95	1.06	0.433	None	N
T641CPCB1*	75	2.95	1.06	0.433	Black	N
T641CPCR1*	75	2.95	1.06	0.433	Red	N

* Material is Copper, 176°C