00 11 02/03 Control Cabinet Keys



- for control cabinets and shutoff systems in the supply of gas, water and electricity
- ► for technical installations in buildings, e. g. air conditioning and ventilation systems, shut-off valves, mains switch-boards, etc.
- ▶ square 6 + 8 mm
- triangular 9 mm


- ► two-way key bit 9 mm dia.
- ▶ with bit insert: slot 1.0 x 7 mm and cross recess PH 2
- ▶ with adapter for 1/4" bits on securing chain
- ▶ zinc die-casting

Model 00 11 02:

► short execution, total length 44 mm

Model 00 11 03:

- long execution, total length 76 mm
- ► additional square of 5 mm





5/7/8

- key for heating, airconditioning, sanitary and building engineering, e. g. for door and window handles or for air bleeding heaters
- ► square 5/7/8 mm
- triangular 10 mm
- conical square

4-10

- ▶ with bit insert: slot 1.0 x 7 mm and cross recess PH 2
- with adapter for 1/4" bits on securing chain
- ► total length: 90 mm
- ▶ zinc die-casting

47

g

75

Length

mm

00	19	Display	Panel

Code

00 11 04

4003773-

048954



- for 12 x 3 pliers
- empty, without pliers and hooks
- assortment on request
- when ordering do always ask for hooks (12 x 00 19 33) and product detail labels
- material: sheet steel, white powder coated, with coloured label

00 19 00 LE

Article-No.	EAN-	Content			47
	Code		Width	Height	
	4003773-		mm	mm	g
00 19 00 LE	034483	empty	480	640	3,400