

Ergonomic, Efficient & Reliable

The new ERG50 and ERG120 tools from Thomas & Betts provide a superior level of reliability and performance, combined with enhanced ergonomics and comfort of use

These ergonomic tools, with adjustable tension and automatic cutting, are ideally suited for efficiently installing all kinds of plastic cable ties in industrial (Original Equipment Manufacturers, Maintenance and Repair Organisations, etc) and construction applications.

Superior reliability and performance

- Developed to meet the market needs for a more rugged and longer lasting tool
- Designed to integrate the greatest number of features in the market

Enhanced ergonomics and comfort of use

- First class design and materials, for maximum convenience
- As a result, the operator is subject to less stress, less fatigue and less risk of trauma due to long term use (such as Carpal Tunnel Syndrome)

Increased efficiency

- Exclusive features for quick set-up and fast installation
- Confidence to achieve a highly professional result

Ordering information

- ERG50 (black nose): for cable tie tensile strength from 80 to 220 N (cable tie width from 2.4 to 4.8 mm)
- ERG120 (orange nose): for cable tie tensile strength from 220 to 540 N (for cable tie width from 4.8 to 7.6 mm)
- ERG50B: spare blade for ERG50
- ERG120B: spare blade for ERG120



Thomas & Betts