

## 95 Cable Cutters, Ratchet Action



95 31 720



- ▶ for cutting copper and aluminium cables, single and multiple wire – also with hard rubber or plastic sheath
- ▶ **not suitable for steel wire and wire ropes**
- ▶ also suitable for cables with iron sheath reinforcement
- ▶ precision ground, hardened blades
- ▶ clean and smooth cut without crushing and deformation
- ▶ little handforce required for cutting due to optimum transmission ratio
- ▶ high cutting capacity due to two-hand operation and ratchet action
- ▶ the blade can be opened in any cutting position
- ▶ suitable for working in confined areas
- ▶ blades made of special tool steel, oil-hardened and tempered
- ▶ handles made of steel tubing

Article-No.	EAN-Code	Head	Handles	Cutting capacity			
				⊗	⊗	⊗	⊗
Length mm	Code 4003773-			⊗	mm <sup>2</sup>	MCM	g
<b>95 31 720</b>	025269	lacquered	powder coated, with plastic handles	60	740	1400	5370
<b>870</b>	025276			100	960	1900	7090
<b>95 39 720</b>	025290	spare moving blade					595
<b>870</b>	025306						1340



**95 31 870:** Large cutting capacity: maximum 100 mm dia. / 960 mm<sup>2</sup>

## 95 Wire Rope Cutter



95 61 190



- ▶ for medium hard wire up to 6 mm dia., e.g. Bowden cords, but also for cables and steel rods
- ▶ with opening spring and locking device
- ▶ cutting edges additionally induction hardened
- ▶ special blade geometry prevents the wire rope fanning out

Article-No.	EAN-Code	Head	Handles	Cutting capacities			⚖
				⊗	⊗	⊗	
Length mm	Code 4003773-			mm <sup>2</sup>	⊗ mm	⊗ mm	g
<b>95 61 190</b>	019640	polished	plastic coated	10	6	4	315