

98 Cable Knife



98 56

Article-No.	EAN-Code	Blade length		
	4003773-	mm	Length	g
98 56	026570	50	185	65
98 56 09	030829	spare blade		


1000 V
 IEC 60900
 DIN EN 60900

- ▶ solid, fixed straight blade
- ▶ replaceable specially ground blade
- ▶ blade made of stainless steel
- ▶ with hinged blade guard, integrated in the handle, captive
- ▶ back of the blade plastic coated to avoid short circuit
- ▶ ergonomically shaped safety handle
- ▶ VDE tested according to DIN EN/IEC 60900

98 Voltage Tester with load application

DUSPOL® compact



98 60 04

Article-No.	EAN-Code	Length		
	4003773-	mm	g	
98 60 04	051961	1400	185	


1000 V
 IEC/EN 61243-3
 DIN VDE 0682-401

- ▶ LED display shows direct and alternating current levels 12, 24, 50, 120, 230, 400 and 750 V
- ▶ polarity test with direct voltage
- ▶ identifying the phase conductor against the protective conductor (PE) in alternating voltage
- ▶ load application to suppress inductive and capacitive voltage at $I_s \leq 200$ mA



- ▶ VDE tested according to DIN EN/IEC 61243-3

DUSPOL® is a registered Trademark of Benning, Elektrotechnik + Elektronik GmbH & Co. KG


98 Insulating Flat Nose Plier

from plastic



98 62 200

Article-No.	EAN-Code		
	4003773-	Length	g
98 62 200	021186	mm	90

 **1000 V**
 IEC 60900: 1995
 DIN EN 60900: 1997

- ▶ especially for meter assembly and meter blocking
- ▶ fully insulating to avoid short circuits
- ▶ fibreglass reinforced plastics
- ▶ tested according to DIN EN 60900: 1997 IEC 60900: 1995