# TouchBoard G80-11900



### **Facts & Features**

- Single mechanical keys with Gold Crosspoint contacts (Cherry MX Modules)
- Designed for continuous use -> 50 Mio key presses
- Robust and reliable
- Space-saving and ergonomic
- Integrated Touchpad plus 2 mouse buttons
- Usable with standard drivers of the operating system
- Ideal for industrial usage and for 19" applications
- Programmable keys (USB version)

# **Agency Approvals**

- CE, VDE/ÜG (EN60950), cURus, FCC VCCI, BSMI (PS/2 version), WHQL
- Designed for Windows<sup>TM</sup> 2000 and XP
- MS Windows<sup>™</sup> Vista, Linux compliant

# **System Requirements**

PS/2: IBM- or compliant system

PS/2 plugs for keyboard and mouse

USB: USB plug & supporting operating system

MS Windows<sup>™</sup> 2000, XP or Vista for

KeyM@n Software

# **Delivery Volume**

- 1 Keyboard
- 1 Printed Manual
- 1 CD-ROM (USB version)
- 1 Adaptor PS/2 → DIN(AT) (Combo version)
- 1 Adaptor PS/2 → RS232 (Combo version)

#### **Technical Data**

Number of Keys:

104 = international layout 105 = european layout (each including Windows<sup>TM</sup> keys)

 Cable Length: approx. 1.75 m

Weight:

approx. 1000 g (keyboard approx. 1200 g (with packaging)

Dimensions:

approx. 415 x 193 x 37 mm (keyboard) approx. 450 x 245 x 45 mm (packaging)

Interface:

USB 2.0 (1.1 compatible) or PS/2

Current Input:

PS/2: approx. 35 mA (keyboard)

approx. 3 mA (Touchpad)

USB: max. 100mA

Touchpad:

Resolution: 1000 dpi

Lifetime (Overlay): > 10 Mio. strokes

Two additional mouse buttons

Reliability:

MCBF > 10<sup>9</sup> operations

MTBF > 100.000 hours

Operating life time of individual keys:

> 50 Mio operations

Storage Temperature:

-20 °C until 60 °C

Operating Temperature:

0 °C until 50 °C

Packaging Unit:

72 keyboards per master carton 2 master cartons per pallet

Warranty:

2 years



# TouchBoard USB Version:

Keys listed below can be programmed via Cherry KeyM@n software (SW macros; max. 3 layers):

Function keys F1 – F12; Insert; Delete; Home; End; Page Up; Page Down;

PrtScr; Break; Numpad Comma; Numpad 0

No support of extended configuration for the touchpad (via software).

Order Number	Interface Keyboard	Interface Touchpad	Colour
G80-11900LUMxx-0	USB		light grey
G80-11900LUMxx-2	USB		black
G80-11900LPMxx-0	PS/2	PS/2	light grey
G80-11900LPMxx-2	PS/2	PS/2	black
G80-11900LTMxx-0	PS/2 (DIN(AT) via Adaptor)	PS/2 (RS 232 via Adaptor)	light grey
G80-11900LTMxx-2	PS/2 (DIN(AT) via Adaptor)	PS/2 (RS 232 via Adaptor)	black

The xx in the order number defines the country version:

## European layout (105 keys):

Belgium ΒE

CH Switzerland

DE Germany

DK Denmark

ES Spain

FΑ France/Arabia

FR France

GB **UK-English** 

GR Greek

ΙT Italy

NO Norway

PO Portugal

SF Sweden/ Finland

TS Czechia

### International layout (104 keys):

EU US-English with €-Symbol

RB US-English/Cyrillic

US **US-English** 

(Other country versions upon request.)

Cherry GmbH Cherrystraße 91275 Auerbach/Opf.

Germany

+49 9643 18 0 Phone: Internet: www.cherry.de

+49 1805 243779 (+49 1805 CHERRY) Sales:

E-Mail: sales@cherry.de Fax: +49 9643 18 1545

The manufacturer accepts no liability for errors or nonavailability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2007 Cherry GmbH, Last update: 10. Jul 2007

