


RoHS Compliant  
Pb - Lead Free

Ltr	Revisions	Date	Appr

**Electrical Specifications:**

Nominal Frequency	40.000	MHz
Mode of Oscillation	Fundamental	-
Frequency Tolerance at 25°C	±10	PPM Max
Frequency Stability over Temperature Range	±10	
Operating Temperature Range (Extended)	-40 to +85	° C
Storage Temperature Range	-55 to +125	
Aging per Year	±3	PPM Max
Load Capacitance	12	pF
Shunt Capacitance (Maximum)	5	
Equivalent Series Resistance (ESR)	50	Ohms Max
Drive Level	100 Typ - 500 Max	uW
Solder Reflow Characteristics	+260 for 10 s Max	° C

**Mechanical Specifications:**



11-3 Chien-Kuo Rd T.E.P.Z. 4027 Taiwan, ROC

All dimensions are millimeters.

CAD: TR

Review: SL

Appr: AL

Page: 1/1 Date: Aug 28, 2008

Specification Title:

**Quartz Crystal Unit  
3.2 x 2.5 mm SMD  
Product Specification  
Farnell Order Code: 1640984**

Part Number: **C3E-40.000-12-1010-X**