
# MODEL

### & Cutters



#### **Retractable Safety** Knife set


Retractable precision knives with blade locking feature. Can be opened and closed with one hand. Ultimate safety. Choice of 4 different scalpel blades or a complete set.


<del></del>	
Safety Knife Set	EKNEZIEK
Green - #10 blade	240.858.678.10
Grey - #10A blade	EM89416/610/4
Yellow - #11 blade	EKNEGA GATA
Red - #15 blade	EKN8216/15


#### Set of 3 Trimaway **Knives**


- Strong disposable knives
- Nylon handles
- Best quality Sheffield steel blades

PKN 1007/3









#### **Cutting Mats**

- 3 layer PVC mat in sandwich structure ensures no cracking or warping. Non slip surface of base holds paper firmly and prevents blade run and cutting error.
- Preserves the life of blades
- Encourages accurate cutting
- Available in the following sizes - A1, A2, A3, A4, A5.
- A1 600 x 900mm PKN6001 A2 - 600 x 450mm PKN6002 A3 - 450 x 300mm 🍇 PKN6008 A4 - 300 x 200mm PKN6004 A5 - 230 x 160mm PKN6005

#### Circle (Compass) Cutter

- Designed for cutting accurate circles in paper, card, masking films, leather. vinyl etc.
- 10mm to 150mm.

#### PKN4101

Replacement Blades PKN4101/B

#### **Plastic Cutter** Scriber

Perfect for scribing and cutting laminated plastics and acrylics. The unique blade design ensures clean smooth scribed lines and leaves no burrs.

#### PKN4150

Replacement Blades PKN//150/B

#### **Rotary Cutters** 28<sub>mm</sub>

Rotary cutters offer a very convenient and efficient way to cut a wide range of materials such as fabric, leather, vinyl, paper, card veneers etc.

PKN6194



Skip Spare blade 28mm PKN6194/S

Wavy Spare Blade 28mm PKN6194/W

#### **Polystyrene Foam Cutter**

- Operates from a
- 4.5V battery
- Cuts material up to 50mm (2") thick
- Cuts any shape

#### PEGENT

Pack of 10 Spare Wire Elements

PECK 12/10


#### Auto-Lock, Heavy **Duty Cutter**


Treated with soft skidproof grip & comfortable handle. Safety lock system for safer use.

#### PKN1068

Spare Blades 18mm x 100mm wide 10 strips PKN1069/E








### Dividers & Calipers

- High quality tool steel
- Micrometer style adjustment

⚠ Inside Calipers 3"/75mm

③ Dividers 3"/75mm EDV6/41/3

**⊙** Outside Calipers 3"/75mm PDV6712/61



#### Stainless Steel Engineers Squares

- Solid steel stock
- Hardened and tempered finely polished blades
- Manufactured to BS939

1"/25mm

PSQ2210/1

2"/50mm


PSQ2210/2

3"/75mm

PS02210/3

4"/100mm PS@2210/4

FOR CALLY



#### 3m/10ft Measuring Tape

- Non slip rubber shell
- Tempered steel spring blade
- Sliding thumb lock
- Belt clip & wrist strap


#### PRU1320




#### 2 Way Pocket Level

- 100mm/4" handy level
- Useful addition to any toolbox

PRU1254





#### **Auto Centre Punch**

Heavy knurled body for easy handling
 Hardened and ground punch point
 Adjustable tension

#### PPU1001



#### Punch 'n' Scribe Auto centre Punch

● This two in one tool can be used as both a slim auto centre punch and scriber. Adjustable tension on centre punch & pocket clip included.



#### Scriber with carbide point

Fully retractable tungsten carbide point (replaceable)
 Unique device to stop point from falling out
 Pocket clip for easy carrying.



#### Super Fine Scriber with 0.5mm Auto Feed point

- Fully retractable Tungsten carbide point (replaceable)
- Device to stop point falling out Pocket clip for easy carrying

#### PSE0930



#### Handy Scriber 175mm

- For marking & scoring wood, metal, laminates and plastic.
- Double ended wint for scribing & wedge knife for scraping.

PSB1412



#### **Machinists Scriber**

Basic single ended scriber L100mm

PSB1216



# MOD CRA

# Probes, Carvers & Broaches

#### An introduc


#### Probes & Carvers

Wax carvers and probes are used by dental technicians and jewellers for carving, shaping and forming models prior to casting. They can also be used for applying, spreading and smoothing soft materials such as clay, modelling compounds, putty, epoxy, wood filler etc.

#### Set of 6 Stainless Steel Carvers

A selection of six quality stainless steel double ended carvers in a useful storage wallet





#### Set of 3 Stainless Steel Carvers


A selection of three quality stainless steel carvers in a useful storage wallet



#### Set of 6 Stainless Steel Probes

A selection of six quality stainless steel double ended probes in a useful storage wallet...

PDT/5197



#### Set of 3 Stainless Steel Probes

A selection of three quality stainless steel probes in a useful storage wallet.



### Probe Handle & 4 Probes

High quality knurled handle can be used with each of the 4 probes to create stable and robust tools for carving, shaping and forming models and workpieces.





#### An introduction to Broaches

Broaches are used for gently enlarging or sizing holes. They can also be used to clean or finish holes which have been drilled previously. As well as cutting broaches, we also have a range of smoothing broaches which can be used to burnish holes after cutting.



#### Cutting Broach Sets

- Contains six cutting steel broaches
- Handy storage wallet

0.4 - 1.4mm

0.6 – 2.0mm

1.2 – 3.0mm




#### Smoothing Broach Sets


- Contains six smooth steel broaches
- Handy storage wallet

0.4 - 1.4mm

0.6 – 2.0mm

1.2 – 3.0mm





Individual Cutting Broach 3.0 to 4.0mm

 Particularly useful for 1/8" model railway axles, this individual broach has a knurled plastic handle and covers a useful range of sizes


PBR2616

# mers and Pin Vices

### Introduction to Drills, Rean

& Pin Vices Successful drilling depends not only on using the right drill bit for the job, but also in using the right techniques to guarantee accuracy. As well as choosing the most suitable drill bit, pay attention to which tool you are going to use for the job in hand. Depending on the material and size of the bit, it could well be that a small Archimedean drill will allow you more control than mounting the bit into an oversize power drill. A little thought will also save you breaking more drills than necessary.

Taper reamers are ideal for finishing and deburring panel holes. These tools can find many uses amongst different hobbyists. Electronics hobbyists will find it useful after drilling project boxes or for making panels etc, whereas model makers will find them useful for deburring holes in a variety of materials.




#### **Archimedean Drill Holders**

- Archimedean drill holders are spiral type hand drills which turn by pushing the knurled centre ring up and down.
- ldeal for all small drill bits up to 1mm
- Ideal for precision drilling
- These are the ideal hand drill holders to use with very small drills as supplied in Model Craft Microbox drill sets PDR4001 and PDR4004


Standard version (illustrated

203444

(with return spring)







#### 20 Piece Microbox Drill Set - Metric

High Speed Steel metric drills from 0.3 to 1.6mm in a handy plastic index box with sliding top. Feeps drills securely in place PDE400 and dispenses one drill at a time.

#### 20 Piece Microbox Drill Set - Wire Gauge (Numbers) \*

Contains one of each HSS number drill, sizes 61 to 80 inclusive in handy sliding top index storage dispenser.

2012/10/2

#### 10 Piece Microbox 2.35mm Shank Drill Set - Metric

- High Speed Steel drills from 0.5 to 2.2mm all with standard 2.35mm size shanks.
- These are designed to be held in a collet or chuck, particularly useful for use with miniature power drills

PD:4005



#### **Pistol Grip Hand Drill**

- Handy and very safe hand drill on which all gears are enclosed. Keyless chuck accepts drill bits up to 6.4mm (1/4")
- Drill compartment in the handle

PDR 1962

# Drills, Re

# s and Pin Vices continued


#### Pin Vice - Double **Ended Swivel** Top

- Handy holder for drills, taps, pins etc
- 2 reversible collets 0-1.2mm, & 1.3-2.4mm 0.8-2.0mm, & 1.8-2.9mm
- Swivel head for comfort and efficiency of use.

Pin Vice only

PPV2287

Pin Vice & 5 drills PP\/2287/P






#### Pin Vice - Double Ended

- Handy holder for drills, taps, pins etc
- 2 reversible collets: 0-1.2mm, & 1.3-2.4mm + 0.8-2.0mm, & 1.8-2.9mm
- Anti-roll 6-sided body

GPVi06i



#### **English Patern Pin Vice**


- Ideal vices for holding small tools, drills, taps etc.
- Knurled body
- Hollow for holding long items
- Capacity: (0-1.0mm, 0.8-1.5mm 1.3-3.1mm, 3.0-4.8mm)

Type 121 Capacity 0-1.0mm PRAGETA Type 122 Capacity 0.8-1.5mm PPV4001/B

Type 123 Capacity 1.3-3.1mm PRAMOVE

Type 124 Capacity 3.0-4.8mm Pay2001/01 Set of 4 Pin Vices


PPV4001/S



#### Wing Nut Hand Vice

- Hand held vice for gripping small components e.g. pins, wire, rods etc. 12.5mm (1/2") jaws are smooth and there is a hole along the centre of the handle to accept long pins and wire. L150mm.
- Max jaw opening 5mm

PPV0004




#### Slide Locking Holder

Hand held vice for gripping small components e.g. pins, wire, rods etc. 

L110mm. 


Max jaw opening 0-1.5mm PPV2002



#### Adaptor Pin Chuck Set with 4 Collets

- For use with miniature drills. Lock this adaptor in chuck to convert it for precise drilling with small size drill bits.
- Supplied with 4 collets.

PPV5155



#### Pin Chuck Set with 3 Collets

- All steel construction
- Blackened finish
- Suplied with 3 collets
- Shaft diameter 6.4mm/¼ inch \* Capacity 0-2.5mm

PPV4012/S

### rvice Aids

#### **Precision** Lubricator


- Complete with general purpose lubricating oil
- Lightweight, easy to use
- ldeal for delicate. precision work
- Delivers small drops of oil as required

#### POL1000


#### Red Transmission oil Lubricator

Specially formulated for use on RC models.

#### POL1002







#### 12ml Curved Syringe including Tip

- General purpose syringe with curved nozzle
- Ideal for liquid application in hard to reach areas
- Multitude of uses



#### POIS012/0

#### Three 5ml **Syringes**

- General purpose syringes
- Ideal for the application of larger liquid quantities
- Supplied in packs of 3


POE 005/8



#### Three 1ml **Syringes**


- General purpose syringes
- Ideal for the application of small liquid quantities
- Supplied in packs of 3

2015(00)/8



#### Rubber Blower

Used by watchmakers for removing dust from watch dials, now available to modellers to blow dust away from awkward areas.



#### PB 1297


#### 2 Piece Set of Double **Head Brushes**

Four useful service brushes on two handles: brass/ steel and hard/soft bristle



#### Inspection mirror

- Perfect for inspecting in awkward places
- Check internal mechanisms without dismantling
- Great for modellers and



#### Display **Turntable**

Battery driven turntable for displaying models. Also a very useful accessory for use when airbrushing circular objects. Max weight 2.5 Kgs. Speed 1.3 rpm






#### PBA9119

#### Mini **Swinger** Organiser


The ideal space saving answer to storing & organising small parts, beads, screws, electronic components, fishing tackle and general accessories

- 8 removable plastic, pocket sized containers
- Simple, easy snaplock lids for securing contents
- 48 versatile compartments -6 in each container
- 8 container cradles that swing open for easy access
- The organiser is fitted with a handle for complete portability and also 3 screw

brackets for wall mounting



Compact size - Space saving



PBX1048

# MODEL CRAFT F

### . Abraders

#### An introduction to File

Abraders The file is the most frequently used tool when working with metal, wood, plastics and a host of other materials, so understanding the correct choice and usage of these tools is very important. There are three criteria required to correctly identify a file - the shape (cross-section), the length and the cut. There are many different cross sections available but the principle ones are flat, square, round and half-round. The length of the file is the distance from the shoulder below the tang to the end of the file. The cut refers to the pattern and density of the teeth.

#### Glass Fibre Pencil - 4mm

Propelling pencil action exposes more or less of the glass fibres. The shorter the fibres showing, the more abrasive the action.

#### PEU 019/1

#### 10 x 4mm Glass Fibre Refills


 Glass fibre refills for use with the 4mm glass fibre pencil (above). Supplied in packs of ten.

#### PBU1019/2/40

#### 10 x 4mm Brass Refills

 Brass refills for use with the 4mm glass fibre pencil (above).
 Supplied in packs of 10

#### 2:U5020*/2/*50






#### Glass Fibre Pencil - 2mm

• Ideal for similar applications to the larger 4mm pencil (above) but perfect for use on smaller and less accessible areas.

#### 5 x 2mm Glass Fibre Refill

Glass fibre refills for use with the 2mm glass fibre pencil (above). Supplied in packs of five.




#### String Bound Glass Fibre Brush

For use on larger areas ● Length 180mm x 10mm dia

PEUi 022/10


PBU2-38/5



#### Set of Three Swiss Style Precision Needle Files


- Precision made in the EC
- Flat, half round & round profiles
- 16cm medium cut 2

PKF344372



#### Universal needle File Handle

- Beautifully turned in hardwood, this handle fits neatly in the hand and has that wonderful feel of quality about it.
- The collet will accept all regular needle files.



#### Set of 5 Diamond Needle files

- Set of five 14cm diamond needle files.
- Longer lasting and faster working than conventional files.

PHL6002

#### 10 Piece Budget Needle File Set

- Set of ten assorted imported needle files in a handy wallet.
- Medium cut, these files represent very good value for money and are ideal for general use

PEL6001




#### 10 Piece Riffler File Set

- Set of 10 useful shape double ended rifflers
- Useful for reaching places not accessible with ordinary needle files

PEL 6003







#### 6 Piece Needle File Set

- Set of 6 140 x 3mm needle files with rubber cushion-grip handles
- Supplied in handy storage box

PFL6004






#### 6 Piece Needle Rasp File Set

Ideal for use on wood or wax for rapid non-clogging material removal

23 6006



#### **Spring-Loaded Finger Sanders**

These sanders have a unique shape for working on both flat and curved surfaces. Choice of

curved surfaces. Choice of widths. Spare sanding bands are available in coarse, medium and fine grades.

10mm sander – medium PF16010 20mm sander – medium PF16020 40mm sander – medium PF16040

#### **Spare Sanding Bands**

 Spare sanding bands are supplied in packs of 3 (one each grit – coarse, medium and fine) 10mm **PF 6010/B** 20mm **PF 6020/B** 40mm **PF 6020/B** 

MODEL Craft

#### **PURE SABLE PAINT BRUSHES**



- Ideal for painting miniatures
- Pure red sable hair
- Red polished triangular handles
- Available individualy or in sets

Size 3/0


Size 2/0

Size 0 PPE2201/0


Size 1

Size 2

Set of 5









#### DIY POLISHING KITS

5 complete sets covering • Brass, copper & soft metals • Stainless Steel & hard metals

• Wood • Plastics • Chrome & plated metals

The range includes: • 4 replacement buffs (mops)

• 8 polishing compound twin packs for preparatory/ finishing work on various materials


• 1 straight shank arbour

#### **Brass & Copper Polishing Kit**

The simple way to polish Brass, Copper, Aluminium and other soft metals

KIT INCLUDES:

- 100mm 10-fold hard buff
- 100mm 10-fold soft buff
- Straight shank arbor for use with chuck
- Brown polishing bar for coarse work and material preparation
- Blue bar for buffing/finishing work




#### **Stainless Steel Polishing Kit**

The simple way to polish Steel, Iron, Stainless and other hard metals

#### KIT INCLUDES:

- 100mm 10-fold hard buff
- 100mm 10-fold soft buff
- 100mm 2-section sisal buff
- Straight shank arbor for use with chuck
- Grey polishing bar for coarse work and material preparation
- Blue bar for stage 2 buffing work
- Pink bar for high finish



#### Wood Polishing Kit

PC1003

The simple way to polish most Hard and Soft Woods


KIT INCLUDES:

- 100mm 10-fold hard buff
- 100mm 10-fold soft buff
- 4-section alu/oxide buff

PC1001

PC1002

- Straight shank arbor for use with chuck
- Buff compound for high finish




#### Plastic Polishing Kit

PC1004

The simple way to polish Plastics, Fibreglass & Bakelite KIT INCLUDES:

- 100mm 10-fold hard buff
- 100mm 10-fold soft buff
- Straight shank arbor for use with chuck
- Brown polishing bar for coarse work & material preparation
- Buff polishing bar for high finish




#### Chrome & Plated Polishing Kit

PC1005

The simple way to polish Chrome and Plated surfaces

KIT INCLUDES:

- 100mm 10-fold hard buff
- 100mm 10-fold soft buff
- Straight shank arbor for use with chuck
- White bar for high finish



# MODEL CRAFT


# Essential and Innovative New tools in the range


The Modelcraft Collection introduces 14 new tools with the Modelmaker, Crafter and DIYer in mind

#### 3 x 15mm Rotary cutter set

- 3 tools for cutting, perforating and scoring card, paper, tin foil, textiles
- Ideal for card making, scrap booking, papercraft
- Inbuilt safety, blade protector

PKN6195/S





#### **Rotating Cutting Mat**


- 31 x 31cm self healing cutting mat
- Dual function stationary or rotating no need to turn your project Makes multiple and special cuts simple & easy
   Includes unique centre piece for fixing or freeing mat; and non slip base mat
- Ideal for painting, clay & pottery, as well as general craft & hobby tasks
- Includes rule, angle and circular measurement

PKN8008

#### 5 piece Mini Diamond File set 100mm

- Ideal for intricate filing especially on small plastic model projects
- 5 shapes for dealing with various shapes and contours

PFL6007





#### Diamond Hand File with wooden handle



• File 75mm x 3mm • Ideal for general purpose filing applications and for reaching into tight slots

PFL6008






#### Pen Grip Pin Pusher

- Pocket sized fastening tool
- Quality wooden handle
- · Ideal for pushing brass or black steel pins
- Great for setting miniature n-gauge rail track on to board, or for nailing tasks on wooden boat models, dolls houses etc
- Can push pins into 9mm plywood!

Pin Pusher	PPUB174
Pin Pusher & 100 Black Pins	8208746
Pin Pusher & 100 Brass Pins	DPU8174E
100 Black Pins	
100 Brass Pins	PRUSWA/RE





#### The Pick & Place tools

The Pick & Place tools are ideal for picking up and pinpoint placing of small objects, such as:

- Beads, rhinestone s, gems, glitters, confetti, punch outs, decals for plastic models, small plastic component, stamps etc
- <sup>●</sup> The tips come in 3 sizes, small, medium & large and are made of a specially formulated acrylic resin to give them the tackiness required
- If the tips lose their adhesion by catching dust or oils, simply roll the tips on adhesive tape to clean them up

Pick&Place Tool – Small (Red)	
Pick&Place Tool - Medium (Blue)	PTW1132
Pick&Place Tool – Large (Green)	PIWH33



#### Multi End Hobby hammer

- Versatile double ended hobby hammer
- Lightweight with Knurled grip for comfortable use
- Includes 6 hammer options that simply screw on
- Ball Pein Dome Flat end Chisel end Plastic Flat end for work on softer material Brass Flat end for work on softer metals Length 185 mm

#### PHA5116

#### LED magnifier Tweezer

- Ideal for picking up small parts and components
- Also for removing splinters
- Includes adjustable magnifier 1.75x magnification
- Comes with LED light

#### PTW1124

#### Bench Universal Work holder

- Excellent support tool for holding odd shapes and smaller components for painting, filing, engraving, sawing & shaping
- The steel pins can be placed anywhere on the head to accommodate various shapes. Also can be used for bending and forming wire
- Head can be removed from base and fitted to a bench vice
- Weight 504g

#### PCL8010/B

### **Economy Sprue** & Plastic Cutter

- For flush cuts in plastics and sprues
- Ideal for making small cuts in plastic models, military figures and other general hobby & craft applications

#### PPL6703




### Clip-on Spectacle eye glasses

- Reduces eye strain
- Ideal for precision & miniature work
- Can clip on tospectacles and adjusted to suit
- Magnification 3x (3.5")

#### POP1038/35





#### Chasing Hammer 1 1/8" (28mm)

- Ideal for shaping, bending and decorating thin metals
- Quality Wood handle, ergonomically designed and balance for comfortable use


PHA8366




## Scriber with fixed carbide point

- Handy scriber with fixed carbide point
- Knurled handle for comfortable grip







#### LED Supporting glasses & 3 magnifiers

- Ideal for close-up precision work leaving your hands free
- Includes 3 adjustable lenses with magnifications 1.5x, 2.5x, 3.5x
- Fitted with LED light (batteries included)

#### POP1768

