

# SPECIAL – TWEEZERS FOR THE SMD – TECHNIQUE

high precision tweezers from special steel  
stainless - matt finish - anti-magnetic - acid-resisting

**5-060 6-piece set ESD-Tweezers for the SMD-Technique**  
with black **ESD-coating**,  
in a wallet made from **conductive** material

The tweezers have been tested with good results adequate to DIN EN 61340-5-1, 61340-2-1, 61340-2-3 for work in ESD-protected areas.

Weight: 155 g

## No. Description of individual tools

- 5-049-13 **SMD-tweezers**, straight, very sharply pointed, 110 mm
- 5-055-13 **SMD-tweezers**, sickle-shaped, very sharply pointed, 120 mm
- 5-059-13 **SMD-tweezers**, flat, rounded tips, 2 mm width, 120 mm
- 5-067-13 **SMD-tweezers**, tip 45° angled, 2,0 mm width, 120 mm
- 5-068-13 **SMD-tweezers**, tip angled, 1,6 mm, 120 mm
- 5-078-13 **SMD-tweezers**, tapering, chisel, 1,0 mm width, 130 mm

