




## STAS 200 grau/grey

Industrial Connectors:Rectangular connectors ST-series:Cable plug

Product description	
Description	Cable plug with strain relief and coding fin
Туре	STAS 200 grau/grey
Order No.	932 038-106
Type of contact	male
Number of contacts	2 + PE
Cable gland	PG 7
Cable diameter	4 mm to 6.5 mm
Conductor size	max. 1.5 mm2
Housing Color	grey
Contact bearer color	black
Drawing	



echnical data Pin dimensions	0
Pin dimensions	0
iii diiiioiioioiio	2 mm
Rated voltage	250 V AC/DC
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
ype of termination	screw
Material Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
lousing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
emperature range	-30 °C to +90 °C
nflammability class	

Housing	UL 94 V-1	
Contact bearer	UL 94 HB	
Approvals		
UL	UL	
VDE	VDE	
SEV	SEV	
Packaging unit		
Packaging unit	100 pieces	
Scope of delivery and accessories		
Accessories to order separately	safety brackets STASI 2, order no. 732 044-000	