



REQUIREMENTS

- 1- CLIP FOR T0220
- 2- FORCE MIN. AT S: 4.5 mm = 16 N
- 3- FORCE MIN. AT S: 5.0 mm = 21 N

scale 1 : 1



Important dimensions

Note:		Scale							
Not dimensioned edges: R 0,5		5 : 1							
THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS		©							
		DR							
<p>AAVID THERMALLOY EUROPE www.aavidthermalloy.com</p> <p>Via XXV Aprile, 32 40057 Cadriano - Bologna ITALY Tel. +39 051 764011 Fax +39 051 764090</p> <p>Cheney Manor SWINDON WILTS SN2 2QN UK Tel. +44 1793 401400 Fax +44 1793 615396</p> <p>COMPANY WITH QUALITY SYSTEM CERTIFIED BY LRQA ISO 9001:2000</p>			Format A4 REV Date Revision description	A 10May07 ORIGINAL (was ZA4426-9)	RT By				
		Die n.	MATERIAL EN10132-4 C67S 42-46 HRC		DRAWING n. 439648				
		Factor	GENERAL TOLERANCES LINEAR ±0,3		Vis. n. 439648		Description: CLIP-STEEL-ZH-W.15.0 SP.0.4 H.19.0-STD		
		Perim.	ANGLES ±3°		Drawn R. Tassinari		ROHS COMPLIANT-(4426G)		
		Area	FINISH Zn high resistance plated		Check				
		Weight	RoHS Compliant						
			Corrosion resistance: 50h Neutral salt						