





THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS

UNCONTROLLED DOCUMENT
CORRECT ONLY ON / /



UNSPECIFIED INTERNAL RADII = R0.5



AAVID THERMALLOY
EUROPE www.avidthermalloy.com

Via XXV Aprile 88
40057 Chiodeno Bologna
ITALY
Tel. +39 051 784011
Fax +39 051 784080

Cheney Manor
Swindon, Wiltshire SN2 2QN
UNITED KINGDOM
Tel. +44 1793 837861
Fax +44 1793 815368

COMPANY WITH QUALITY SYSTEM
CERTIFIED BY LLOYDS
= ISO 9001:2000 =

Die n.	MATERIAL D.4mm BSI 449 CS70 AUST 525-575	6	16Dec05	SURFACE FINISH CHANGED FOR ROHS COMPLIANCE. ECF UK2289 REFERS.	SM	DRAWING n.		
Factor	GENERAL TOLERANCES	5	01Dec04	SURFACE FINISH CHANGED. ECF UK2164 REFERS.	SM	ZA4473		
Perim.	±0.3, ANGLES ±2° UNLESS OTHERWISE STATED	4	03Sep00	WIDTH DIMENSION CHANGED	AE	Vis. n. 439649		
Area	FINISH MECHANICAL ZINC PLATE	3	29Jun99	DEVICE GAP CHANGED	BL	Description:		
Weight	TRIVALENT CLEAR PASSIVATE AND JS 500 SEAL	2	04Jan99	FINISH COLOUR REVISED	TH	4473G TD21B/TD247 SPRING CLP		
Note:	ALL DIMENSIONS IN MM	1	28Aug91	ORIGINAL	TH	Format	Scale	3
Drawn	FF	REV	Date	Revision description	Approved	A4	NTS	
Check								