



DC840KB-GB

12 Volt Compact Cordless Impact Wrench

Selling Proposition

- Durable frameless high speed motor delivers up to 160 Nm of torque
- All metal gearing for efficient power transmission and long tool life
- Aluminium front housing provides greater heat dispersion increasing motor life
- Improved variable speed switch and electronic motor brake for complete control for both setting and removing fasteners
- 1/2" square drive allows for quick and easy bit changes
- Compact body enables use in tight spaces

Standard Equipment

- 30 minute charger
- 2 batteries
- Heavy duty carrying case

Warranty Specifications

- 1 year free service contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Voltage	12 V
Battery Capacity	NiMH 2.6 Ah
Bit Holder	1/2"
Power Output	220 Watts
No Load Speed	0-2400 rpm
Impacts per Minute	0-2700 ipm
Max. Torque	160 Nm
Max. Bolt Diameter	M16