

# AC Current Clamp-on Adaptor Model : CP-09

## Technical Specifications

Function	Range	Output	Sensitivity	Accuracy (of reading)
AC Current (50/60Hz)	0~200A	1mV/A	1A/mVAC	±2.0% ±0.5A

**Output Impedance :** <1k $\Omega$

**AC Bandwidth :** 40 to 400Hz

**Jaw Opening :** 16mm

**Operating conditions :** 0°C to 30°C (32°F to 86°F) 90%RH; 30°C to 40°C (86°F to 104°F) 75%RH; 40°C to 50°C (104°F to 122°F) 45%RH

**Storage conditions :** -22°F to 140°F (-30°C to 60°C); <90% Relative Humidity

**Altitude :** Operate at less than 3000 meters

**Weight :** 129g

**Dimensions :** 111 x 50 x 33mm (H x W x D)

**Standards :** IEC1010-1 (1995); EN61010-1 (1995) Category II 600V, Category III 300V.

