



SANDVIK BELZER

**Double head socket spanner
Metric**



DIN 896-B


Finish: nickel and chrome-plated, fine-polished.

Material: SPECIAL STEEL of CHROME-MOLYBDENUM.

Tubular, straight.

1936M



Product code	EAN code 731415+		Dim mm	L mm	d ₁ mm	d ₂ mm	T-bar Ø mm	
1936M-6-7	1051389	5	6x7	102	10	11	6	25
1936M-8-9	1051396	5	8x9	102	13	14	6	35
1936M-8-10	1830137	5	8x10	117	13,5	16	6	65
1936M-10-11	1051402	5	10x11	117	16	17	8	65
1936M-10-13	1344146	5	10x13	137	16	20	8	95
1936M-12-13	1051419	5	12x13	137	19	20	8	95
1936M-13-17	1830144	5	13x17	147	20,5	25,5	10	160
1936M-14-15	1051426	5	14x15	137	21	22,5	8	95
1936M-14-17	1051129	5	14x17	147	21,5	25,5	10	160
1936M-16-17	1051433	5	16x17	147	24	25,5	10	160
1936M-17-19	1051136	5	17x19	152	25,5	28	12	180
1936M-18-19	1051440	5	18x19	152	26,5	28	12	180
1936M-19-22	1051150	5	19x22	162	28	31,5	12	215
1936M-20-22	1830151	5	20x22	162	29	31,5	12	215
1936M-21-23	1830168	5	21x23	162	30,5	33	14	265
1936M-22-24	1830175	5	22x24	177	32	34,5	14	285
1936M-24-26	1830182	5	24x26	177	34,5	37	14	350
1936M-24-27	1051181	5	24x27	177	34,5	38	14	350
1936M-25-28	1830199	1	25x28	192	35,5	39	16	380
1936M-30-32	1051501	1	30x32	192	41,5	44	16	450
1936M-30-34	1838577	1	30x34	210	40,5	44	16	502
1936M-36-41	1830205	1	36x41	213	50	56	18	730
1936M-46-50	1830212	1	46x50	233	62	66,5	20	950



Mikroskop

Finish: nickel and chrome-plated.
Material: SPECIAL STEEL.

Stepped tommy bar

Product code	EAN code 731415+		T-bar Ø mm	L mm	
26S-610	1830229	1	6 8 10	195	110
26S-1216	1830236	1	12 14 16	390	585

26S

