


# PRODUCT DATA SHEET

Type	Size	Rating	Description	Part No.
Incandescent	G11(G-3½)	12V 2.2W	11mm Bayonet lamp	G643-5



TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13.5	177	196	216	12.8	16.0	19.2	3,000

**NOTES:**

- 1 RoHS compliant
- 2 Cap type BA9s/13, nickel plated brass
- 3 Filament shape C-2V
- 4 Cap marking CML 12V 2.2W

Issue No.	Date	C.N. No.	Drawn	Tech	QA
1	29/08/07	-	BCW		