

# 1.3MHz/3MHz Step-Up DC/DC Converters with Integrated Schottky in ThinSOT

# **FEATURES**

- Integrated Schottky Rectifier
- Fixed Frequency 1.3MHz/3MHz Operation
- High Output Voltage: Up to 38V
- Low V<sub>CFSAT</sub> Switch: 260mV at 250mA
- 12V at 70mA from 5V Input
- 5V at 115mA from 3.3V Input
- Wide Input Range: 2.5V to 16V
- Uses Small Surface Mount Components
- Low Shutdown Current: <1µA</p>
- Soft-Start
- Low Profile (1mm) SOT-23 (ThinSOT<sup>™</sup>) Package

#### **APPLICATIONS**

- Digital Cameras
- CCD Bias Supply
- XDSL Power Supply
- TFT-LCD Bias Supply
- Local 5V or 12V Supply
- Medical Diagnostic Equipment
- Battery Backup

## DESCRIPTION


The LT $^{\circ}$ 3461/LT3461A are general purpose fixed frequency current mode step-up DC/DC converters. Both devices feature an integrated Schottky and a low V<sub>CESAT</sub> switch allowing a small converter footprint and lower parts cost. The LT3461 switches at 1.3MHz while the LT3461A switches at 3MHz. These high switching frequencies enable the use of tiny, low cost and low height capacitors and inductors. The constant switching frequency results in predictable output noise that is easy to filter, and the inductor based topology ensures an input free from switching noise typically present with charge pump solutions. The high voltage switch in the LT3461/LT3461A is rated at 40V making the device ideal for boost converters up to 38V.


The LT3461/LT3461A are available in a low profile (1mm) SOT-23 package.

(T), LTC and LT are registered trademarks of Linear Technology Corporation. ThinSOT is a trademark of Linear Technology Corporation.

# TYPICAL APPLICATION

5V to 12V, 70mA Step-Up DC/DC Converter








# **ABSOLUTE MAXIMUM RATINGS**

#### (Note 1)

Input Voltage (V <sub>IN</sub> )	16V
V <sub>OUT</sub> , SW Voltage	
FB Voltage	
SHDN Voltage	
Operating Ambient	
Temperature Range (Note 2)	40°C to 85°C
Maximum Junction Temperature	125°C
Storage Temperature Range	-65°C to 150°C
Lead Temperature (Soldering, 10 sec)	300°C

# PACKAGE/ORDER INFORMATION



Consult LTC Marketing for parts specified with wider operating temperature ranges.

# **ELECTRICAL CHARACTERISTICS** The ullet denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25 \,^{\circ}\text{C}$ , $V_{IN} = 3V$ , $V_{\overline{SHDN}} = 3V$ , unless otherwise noted.


PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
Minimum Operating Voltage			2.5			V
Maximum Operating Voltage					16	V
Feedback Voltage		•	1.235 1.225	1.255	1.275 1.280	V
Feedback Line Regulation				0.005		%/V
FB Pin Bias Current		•		40	100	nA
Supply Current	FB = 1.3V, Not Switching SHDN = 0V			2.8 0.1	3.6 0.5	mA μA
Switching Frequency (LT3461A)		•	2.1	3.0	3.9	MHz
Switching Frequency (LT3461)		•	1.0	1.3	1.7	MHz
Maximum Duty Cycle (LT3461A)		•	82			%
Maximum Duty Cycle (LT3461)		•	92			%
Switch Current Limit			300	420	600	mA
Switch V <sub>CESAT</sub>	I <sub>SW</sub> = 250mA			260	350	mV
Switch Leakage Current	V <sub>SW</sub> = 5V			0.01	1	μА
Schottky Forward Voltage	I <sub>SCHOTTKY</sub> = 250mA			800	1100	mV
Schottky Reverse Leakage	$V_{OUT} - SW = 40V$			0.03	4	μА
SHDN Voltage High			1.5			V
SHDN Voltage Low					0.4	V
SHDN Pin Bias Current				35	50	μА


**Note 1:** Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.


**Note 2:** The LT3461E/LT3461AE is guaranteed to meet specifications from 0°C to 70°C. Specifications over the -40°C to 85°C operating temperature range are assured by design, characterization and correlation with statistical process controls.


TECHNOLOGY TECHNOLOGY


# TYPICAL PERFORMANCE CHARACTERISTICS




















# PIN FUNCTIONS

**SW (Pin 1):** Switch Pin. Connect inductor here. Minimize trace at this pin to reduce EMI.

**GND (Pin 2):** Ground Pin. Tie directly to local ground plane.

**FB** (**Pin 3**): Feedback Pin. Reference voltage is 1.255V. Connect resistor divider tap here. Minimize trace area at FB. Set  $V_{OUT}$  according to  $V_{OUT}$  = 1.255V (1 + R1/R2).

**SHDN** (**Pin 4**): Shutdown Pin. Tie to 1.5V or higher to enable device; 0.4V or less to disable device. Also functions as soft-start. Use RC filter (47k, 47nF typ) as shown in Figure 1.

**V<sub>OUT</sub> (Pin 5):** Output Pin. Connect to resistor divider. Put capacitor close to pin and close to GND plane.

**V<sub>IN</sub> (Pin 6):** Input Supply Pin. Must be locally bypassed.

# **BLOCK DIAGRAM**




Figure 1. Block Diagram

# **OPERATION**

The LT3461/LT3461A uses a constant frequency, current mode control scheme to provide excellent line and load regulation. Operation can be best understood by referring to the block diagram in Figure 1. At the start of each oscillator cycle, the SR latch is set, which turns on the power switch Q1. A voltage proportional to the switch current is added to a stabilizing ramp and the resulting sum is fed into the positive terminal of the PWM comparator A2. When this voltage exceeds the level at the negative input of A2, the SR latch is reset turning off the power switch. The level at the negative input of A2 is set by the error amplifier A1, and is simply an amplified version of the difference between the feedback voltage and the reference voltage of 1.255V. In this manner, the error amplifier sets the correct peak current level to keep the output in regulation. If the error amplifier's output increases, more current is delivered to the output; if it decreases, less current is delivered.

#### **Layout Hints**

The high speed operation of the LT3461/LT3461A demands careful attention to board layout. You will not get advertised performance with careless layout. Figure 2 shows the recommended component placement.




Figure 2. Suggested Layout

**TLINEAR** 

# APPLICATIONS INFORMATION

#### **Inrush Current**

The LT3461 has a built-in Schottky diode. When supply voltage is applied to the  $V_{\text{IN}}$  pin, the voltage difference between  $V_{\text{IN}}$  and  $V_{\text{OUT}}$  generates inrush current flowing from input through the inductor and the Schottky diode to charge the output capacitor. The maximum nonrepetitive surge current the Schottky diode in the LT3461 can sustain is 1.5A. The selection of inductor and capacitor value should ensure the peak of the inrush current to be below 1.5A. In addition, turn-on of the LT3461 should be delayed until the inrush current is less than the maximum current limit. The peak inrush current can be calculated as follows:

$$I_{P} = \frac{V_{IN} - 0.6}{\sqrt{\frac{L}{C}} - 1} \cdot exp \left( -\frac{\pi}{2\sqrt{\frac{L}{C}} - 1} \right)$$

where L is the inductance, r is the resistance of the inductor and C is the output capacitance.

Table 3 gives inrush peak currents for some component selections.

**Table 3. Inrush Peak Current** 

V <sub>IN</sub> (V)	L (µH)	<b>C</b> (μ <b>F</b> )	I <sub>P</sub> (A)
5	4.7	1	1.1
5	10	1	0.9

#### **Thermal Considerations**

Significant power dissipation can occur on the LT3461 and LT3461A, particularly at high input voltage. Device load, voltage drops in the power path components, and switching losses are the major contributors. It is important to measure device power dissipation in an application to ensure that the LT3461 does not exceed the absolute maximum operating junction temperature of 125°C over the operating ambient temperature range. Generally, for supply voltages below 5V the integrated current limit function provides adequate protection for nonfault conditions. For supply voltages above 5V, Figures 3a and 3b show the recommended operating region of the LT3461 and LT3461A, respectively. These graphs are based on 250mW on-chip dissipation. Improvement of these

numbers can be expected if the LT3461 is supplied from a separate low voltage rail.




Figure 3a. LT3461 Operating Region




Figure 3b. LT3461A Operating Region

#### **Switching Frequency**

The key difference between the LT3461 and LT3461A is the faster switching frequency of the LT3461A. At 3MHz, the LT3461A switches at twice the rate of the LT3461. The higher switching frequency of the LT3461A allows physically smaller inductors and capacitors to be used in a given application, but with a slight decrease in efficiency and maximum output current when compared to the LT3461. Generally if efficiency and maximum output current are crucial, or a high output voltage is being generated, the LT3461 should be used. If application size and cost are more important, the LT3461A will be the better choice.



3461af

# APPLICATIONS INFORMATION

#### Inductor Selection

The inductors used with the LT3461/LT3461A should have a saturation current rating of 0.3A or greater. If the device is used in an application where the input supply will be hot-plugged, then the saturation current rating should be equal to or greater than the peak inrush current. For the LT3461, an inductor value between  $10\mu H$  and  $47\mu H$ , depending upon output voltage, will usually be the best choice for most designs. For the LT3461A, inductor values between  $4.7\mu H$  and  $15\mu H$  inductor will suffice for most applications. For best loop stability results, the inductor value selected should provide a ripple current of 70mA or more. For a given  $V_{IN}$  and  $V_{OUT}$  the inductor value to use with LT3461A is estimated by the formula:

L (in microhenries) = 
$$\frac{D \cdot V_{IN} \cdot \sqrt{V_{OUT}} \cdot 1sec}{1A \cdot \sqrt{1V}}$$

where D = 
$$\frac{V_{OUT} + 1V - V_{IN}}{V_{OUT} + 1V}$$

Use twice this value for the LT3461.

#### **Capacitor Selection**

Low ESR capacitors should be used at the output to minimize the output voltage ripple. Multilayer ceramic capacitors using X5R/X7R dielectrics are preferred as they

have a low ESR and maintain capacitance over wide voltage and temperature range. A  $2.2\mu F$  output capacitor is sufficient for most applications using the LT3461, while a  $1\mu F$  capacitor is sufficient for most applications using the LT3461A. High output voltages typically require less capacitance for loop stability. Always use a capacitor with sufficient voltage rating.

Either ceramic or solid tantalum capacitors may be used for the input decoupling capacitor, which should be placed as close as possible to the LT3461/LT3461A. A 1 $\mu$ F capacitor is sufficient for most applications.

#### **Phase Lead Capacitor**

A small value capacitor can be added across resistor R1 between the output and the FB pin to reduce output perturbation due to a load step and to improve transient response. This phase lead capacitor introduces a polezero pair to the feedback that boosts phase margin near the cross-over frequency. The following formula is useful to estimate the capacitor value needed:

$$C_{PL} = \frac{500k\Omega}{B2} \bullet 1pF$$

For an application running  $50\mu A$  in the feedback divider, capacitor values from 10pF to 22pF work well.

# TYPICAL APPLICATIONS






Figure 4. 5V to 12V with Soft-Start Circuit (LT3461A)




TECHNOLOGY TECHNOLOGY

# TYPICAL APPLICATIONS

#### 3.3V to 5V Step-Up Converter (LT3461A)




#### 3.3V to 5V Step-Up Converter Efficiency



# PACKAGE DESCRIPTION

#### S6 Package 6-Lead Plastic TSOT-23

(Reference LTC DWG # 05-08-1636)




- 1. DIMENSIONS ARE IN MILLIMETERS
- 2. DRAWING NOT TO SCALE
- 3. DIMENSIONS ARE INCLUSIVE OF PLATING
- 4. DIMENSIONS ARE EXCLUSIVE OF MOLD FLASH AND METAL BURR
- 5. MOLD FLASH SHALL NOT EXCEED 0.254mm
- 6. JEDEC PACKAGE REFERENCE IS MO-193




# TYPICAL APPLICATIONS


#### Low Profile (1mm) 3.3V to 15V Step-Up Converter




#### 5V to 36V Step-Up Converter (LT3461)




#### 3.3V to 15V Efficiency



#### 5V to 36V Efficiency



#### 3.3V to ±5V Dual Output Converter



# **RELATED PARTS**

PART NUMBER	DESCRIPTION	COMMENTS
LT1615/LT1615-1	300mA/80mA (I <sub>SW</sub> ) Constant Off-Time, High Efficiency Step-Up DC/DC Converter	$V_{IN}$ : 1.2V to 15V, $V_{OUT(MAX)}$ = 34V, $I_Q$ = 20 $\mu$ A, $I_{SD}$ <1 $\mu$ A, ThinSOT Package
LT1944/LT1944-1	Dual Output 350mA/100mA (I <sub>SW</sub> ), Constant Off-Time, High Efficiency Step-Up DC/DC Converter	$V_{IN}$ : 1.2V to 15V, $V_{OUT(MAX)}$ = 34V, $I_Q$ = 20 $\mu$ A, $I_{SD}$ <1 $\mu$ A, MS Package
LTC3400/LTC3400B	600mA (I <sub>SW</sub> ), 1.2MHz, Synchronous Step-Up DC/DC Converter	$V_{IN}$ : 0.85V to 5V, $V_{OUT(MAX)}$ = 5V, $I_Q$ = 19 $\mu$ A/300 $\mu$ A, $I_{SD}$ <1 $\mu$ A, ThinSOT
LT3460	0.32A (I <sub>SW</sub> ), 1.3MHz, High Efficiency Step-Up DC/DC Converter	$V_{IN}$ : 2.5V to 16V, $V_{OUT(MAX)}$ = 36V, $I_Q$ = 2mA, $I_{SD}$ <1 $\mu$ A, SC70, ThinSOT Packages
LT3465/LT3465A	Constant Current, 1.2MHz/2.7MHz, High Efficiency White LED Boost Regulator with Integrated Schottky Diode	$V_{IN}$ : 2.7V to 16V, $V_{OUT(MAX)}$ = 34V, $I_Q$ = 1.9mA, $I_{SD}$ <1 $\mu$ A, ThinSOT Package

3461af