



PMS 4

Industrial Connectors:Measuring and Testing Equipment:Sets/Accessories:4 mm system

Product description

Description Test equipment set for 4 mm system.
 2 x Clamp-type test probe KLEPS 30
 2 x Test-Probe PRUEF 2
 2 x Crocodile clip AK 2 S
 2 x Test lead MLN 100/1

Type PMS 4

Order No. 932 793-001

System 4 mm system

Cable length 100 cm

Conductor size 1 mm²

Cable material PVC

Cable color Each article in black and red.

Housing Color Each article in black and red.

Clamping range 4 mm - 9,5 mm

Technical data

Pin dimensions 4 mm

Type of contact pin (spring-loaded), socket

Type of termination 4 mm socket, screw

Cable type LEH-XY

Cable specification highly flexible lead

Wire stranding 259 x 0,07

Rated voltage DC 60 V

Environmental conditions

Temperature range -15 °C to +70 °C