

EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk Web: www.edl-lighting.co.uk

Haloflex Lumimaire

The Haloflex range is designed for maximum positioning flexibility in the head movement. The flexible gooseneck arm is either 150mm or 700mm long. A 12/24 volt 20 watt halogen lamp is supplied in either IP 21 or IP 54 version. The product is available with or without a transformer in the base. A range of accessories are available to increase the advantages of this luminaire

Version: HAL-L-IP54-20W-12V-NT Order Code 00609



Dimensional line drawing when available

Primary voltage: 12v

Secondary voltage: Not applicable Lamp type: Halogen Wattage: 20 watt

Lamp base type

Switch fitted Yes/No: Yes
Switch location: On Head
IP Rating IP54

Base Type: Screw down

Fixing: Can be horizontal or vertically mounted

No of arms:

Length of arms 700mm flexible
Arm Material: Covered flexible steel

Shade size and material: 70mm diameter moulded plastic

Shield fitted: Yes
Shield material Glass
Visor fitted: No
Articulation movement: Flexible
Joint type: Flexible
Trailing cable: Yes

Plug fitted Yes (car type - can be removed for hard wiring)

Manufacturing Standard: BS EN 60598 RHOS compliant Not applicable WEE Compliant Not applicable

Finish & Colour: Black





EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk Web: www.edl-lighting.co.uk

The Haloflex range is designed for maximum positioning flexibility in the head movement. The flexible gooseneck arm is either 150mm or 700mm long. A 12/24 volt 20 watt halogen lamp is supplied in either IP 21 or IP 54 version. The product is available with or without a transformer in the base. A range of accessories are available to increase the advantages of this luminaire

Version: HAL-L-IP54-20W-12V-NT Order Code 00609

Features

Variety of Input voltages
Choice of arm lengths
20 watt halogen lamp fitted
Screw down base
Switch on head
Protective lens available (optional extra)
Option accessories include wall bracket, magnet, lens cover and clamp

Clamp Magnet Wall Bracket









Clamp Fitted to Base



Magnet Fitted Wall Bracket to Base Fitted to Base

