

## Farnell Components

### CABLE

Item	Order No.	Type	Description	Colour
12a	60.7456-21 (Comprising 5m hank)	FLEXI-ZW 2,0	Highly flexible, twin-core, PVC insulated cable.	Black 432712-5
12b	60.7456-21 (Comprising 25m reel)	FLEXI-ZW 2,0	As above	Black 432713-5

- Nominal cross section: 2 x 2,0mm<sup>2</sup> / 14AWG
- Strand design: 525 x 0.07
- Conductor diameter: 2.0mm
- Insulation thickness: 0.45mm
- Outer diameter: 3.9mm (h) x 7.9mm (b)
- Current rating: 24 Amp
- Nominal voltage: 1000V
- Test voltage: 8000Vac
- Insulation: PVC
- Operating temperature: -10°C +70°C
- UL: UL approved for test leads, upto +60°C