

SPECIFICATION OF HR-4/5AU

Type: Nickel-Metal Hydride Battery			Size : 4/5A
Capacity ¹⁾		Typical	2150mAh
		Minimum	1900mAh
Nominal Voltage			1.2V
Charging Current x Time		Fast Charge ²⁾	2150mA x about 1.1h
Ambient Temp.	Charge Condition	Fast Charge ²⁾	0~40 ° C
	Discharge Condition		0~50 ° C
	Storage Condition	~30days	-20~50 ° C
		30~90days	-20~40 ° C
		90days~1year	-20~30 ° C
	Internal Impedance ³⁾ (after discharge to E.V.=1.0V)		
Weight ⁴⁾			about 35g
Size ⁴⁾ : (Diameter) x (Height)			17.0 x 43.0 mm

1)Charge: 0.1C×16h, Discharge: 0.2C(E.V.=1.0V) at 25°C

2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.