



Metric Coarse Dienut

| | |
|--------------------------|-----------------------------------|
| Tolerance | 6g |
| Chamfer Lead | 2 Threads |
| Surface Treatment | Bright |
| Application | For reclamation of screw threads. |

| Entry Code | M | P mm | S inch /" | h ₁ inch /" | Entry Code | M | P mm | S inch /" | h ₁ inch /" |
|------------|----|------|-----------|------------------------|------------|----|------|-----------|------------------------|
| F302M3 | 3 | 0,50 | 0.71 | 1/4 | F302M14 | 14 | 2,00 | 1.30 | 5/8 |
| F302M4 | 4 | 0,70 | 0.71 | 1/4 | F302M16 | 16 | 2,00 | 1.30 | 5/8 |
| F302M5 | 5 | 0,80 | 0.71 | 1/4 | F302M18 | 18 | 2,50 | 1.48 | 11/16 |
| F302M6 | 6 | 1,00 | 0.71 | 1/4 | F302M20 | 20 | 2,50 | 1.48 | 11/16 |
| F302M7 | 7 | 1,00 | 0.82 | 5/16 | F302M22 | 22 | 2,50 | 1.67 | 13/16 |
| F302M8 | 8 | 1,25 | 0.82 | 5/16 | F302M24 | 24 | 3,00 | 2.05 | 15/16 |
| F302M9 | 9 | 1,25 | 0.92 | 3/8 | F302M27 | 27 | 3,00 | 2.22 | 1.1/16 |
| F302M10 | 10 | 1,50 | 0.92 | 3/8 | F302M30 | 30 | 3,50 | 2.22 | 1.1/16 |
| F302M11 | 11 | 1,50 | 1.01 | 7/16 | F302M33 | 33 | 3,50 | 2.58 | 1.1/8 |
| F302M12 | 12 | 1,75 | 1.10 | 1/2 | F302M36 | 36 | 4,00 | 2.76 | 1.1/4 |