





LOC		DIST		REVISIONS					
F		7		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A	REVISED PER EC00-7417-98	17-FEB-98	MP	JL
					B	ADDED DESIGN OF PN 144969-2 AND REMOVAL SHEET 2/2	14-DEC-01	MP	JL



FOR PN 144969-1 AND -3
SAME DIMENSIONS AND DESIGN
AS 144969-2 EXCEPTED AS SHOWN.

PART NUMBER	4 CONTACT POINTS	AR. CAGE INOX SPRING	CRIMP AREA
144969-3	Au 0.4 to 0.8µm	Sn 0.8 to 3.3 µm	Sn 0.8 to 3.3 µm
144969-2	Au 0.4 to 0.8µm	Au 0.4 to 0.8µm	Sn 0.8 to 3.3 µm
144969-1	Sn 0.8 to 2µm pretinned	Sn 0.8 to 2µm pretinned	Sn 0.8 to 2µm pretinned

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.ELISEI 18-NOV-93	AMP AMP DE FRANCE 95301 PONTOISE	
		CHK J.LALANGE 24-SEP-98		
		APVD J.J.REVIL 24-SEP-98	NAME	
DIMENSIONS: mm		PRODUCT SPEC 108-18030	CLIP MQS A SERTIR (0.2-0.6mm2) MQS RECEPTACLE WITH BARRIER-CRIMP VERSION	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLC ±0.2 1-PLC ±0.2 2-PLC ±0.2 3-PLC ±0.2 4-PLC ±0.2 ANGLES ±5° FINISH		APPLICATION SPEC 114-15077		
MATERIAL VOIR TABLEAU		WEIGHT 0.2g	SIZE A2	CAGE CODE 00709
		CUSTOMER DRAWING	DRAWING NO C- 144969	RESTRICTED TO -
		SCALE 10:1	SHEET 1	OF 1
			REV B	