



Desk Top & Wall Mount AC-DC Power Adaptors

Single Outputs
40-65 Watts
Universal AC Input

MODELS

PART NUMBER	POWER RATING	O/P VOLTAGE	MAX. O/P CURRENT (A)
PSD40-05-02	40	5	8.00
PSD40-12-02	40	12	3.34
PSD40-18-02	40	18	2.23
PSD40-20-02	40	20	2.00
PSD45-12-02	45	12	3.75
PSD45-15-02	45	15	3.00
PSD45-16-02	45	16	2.82
PSD45-18-02	45	18	2.50
PSD45-19-02	45	19	2.37
PSD45-20-02	45	20	2.25
PSD45-24-02	45	24	1.88
PSD60-12-02	60	12	5.00
PSD60-15-02	60	15	4.00
PSD60-16-02	60	16	3.75
PSD60-19-02	60	19	3.15
PSD60-20-02	60	20	3.00
PSD60-22-02	60	22	2.67
PSD65-12-02	65	12	5.40
PSD65-18-02	65	18	3.60
PSD65-24-02	65	24	2.70
PSD65-48-02	65	48	1.30



ELECTRICAL SPECIFICATION

Plug type: Universal Adaptors or AC Mains Lead

AC Input Voltage: 90~264 Vac

AC Input Frequency: 47~63 Hz

AC Input Current: 2A RMS Max.

No. of Outputs: Single O/P

Load Regulation: +/-5%

Min. Load: 0A

Operation Temperature: 0-40°C

Protection: Short, Over Voltage, Over Current

MTBF: 35 000 Hours

Hold Up Time: 10 ms

Safety: cUL, TUV-PS/GS, CB, CE, PSE

Weight: 330 grams

Dimension: 115 mm (L), 49.3 mm (W), 30 mm (H)